

# GÖSTERGE VE PARK AYDINLATMA AMPULLERİ, 12 V

## Ekonomik

Gösterge panelleri ve konsol aydınlatmaları için ampuller



Res.	Model tanımı	Volt	Watt	Soket tipi	Art.-Nr.	Amb./Ad.
A	-	12	1.2	W2 x 4,6d	<b>0720 160 1</b>	10
B	-	12	2	W2 x 4,6d	<b>0720 160 5</b>	10
C	Clear	12	0.36	W2 x 4,6d	<b>0720 162 4</b>	10
D	W3W	12	3	W2, 1 x 9,5d	<b>0720 161 1</b>	10
E	-	12	2	BA9s	<b>0720 151 1</b>	10
F	T4W	12	4	BA9s	<b>0720 150 1</b>	10
G	-	12	4	BA9s	<b>0720 152 1</b>	10
H	-	12	3	BA7s	<b>0720 155 1</b>	10

## Sofit ampuller



Model tanımı	Volt	Watt	Ölçüler (mm)			Soket tipi	Art.-Nr.	Amb./Ad.
			Uzunluk A	Cam ampulün genişliği B	Temas C			
Kontrol kalem lambası	12	3	21 (+/-1)	6.2 (+/-1)	3.5	SV 7 - 8	<b>0720 177 1</b>	10
-	12	3	27 (+/-1)	8.2 maks.	3.5	SV 7 - 8	<b>0720 170 1</b>	10
C5W	12	5	35 (+/-1)	11 maks.	3.5	SV 8.5 - 8	<b>0720 171 1</b>	10
C5W Gün ışığı	12	5	35 (+/-1)	11 maks.	3.5	SV 8.5 - 8	<b>0720 171 16</b>	10
-	12	5	40 (+/-1)	11 maks.	3.5	SV 8.5 - 8	<b>0720 172 1</b>	10
-	12	6	31 (+/-2)	6.0 (+/-0.5)	3.5	SV 8.5 - 8	<b>0720 171 10</b>	10
Japon versiyon	12	10	31 (+/-2)	10 (+/-0.5)	3.5	SV 8.5 - 8	<b>0720 173 51</b>	10
-	12	10	40 (+/-1)	11 maks.	3.5	SV 8.5 - 8	<b>0720 173 1</b>	10
-	12	15	41 (+/-1)	15.5 maks.	3.5	SV 8.5 - 8	<b>0720 174 1</b>	10
-	12	18	41 (+/-1)	15.5 maks.	3.5	SV 8.5 - 8	<b>0720 175 1</b>	10
C21W	12	21	41 (+/-1)	15.5 maks.	3.5	SV 8.5 - 8	<b>0720 176 1</b>	10

12 volt

24 volt

12/24 volt

HID Ampul