

DARBELİ MATKAP UCU SDS-PLUS DUO-S VARIO



İyi bir delme hızı için iki kesici kenarlı merkezleme ve helis kısmı güçlendirilmiş darbeli matkap ucu.

Çap (Ø)	Uzunluk	Çalışma Uzunluğu	Art.-Nr.	Amb./Ad.
6,5 mm	260 mm	200 mm	0648 556 526	2/10
6,5 mm	310 mm	250 mm	0648 556 531	2/10
6,5 mm	450 mm	390 mm	0648 556 545	1
7 mm	160 mm	100 mm	0648 557 016	2
7 mm	250 mm	190 mm	0648 557 025	2
7 mm	450 mm	390 mm	0648 557 045	1
8 mm	110 mm	50 mm	0648 558 011	2/10
8 mm	160 mm	100 mm	0648 558 016	2/10/50
8 mm	210 mm	150 mm	0648 558 021	2/10
8 mm	260 mm	200 mm	0648 558 026	2/10
8 mm	310 mm	250 mm	0648 558 031	2
8 mm	400 mm	340 mm	0648 558 040	1
8 mm	460 mm	400 mm	0648 558 046	1
8 mm	600 mm	540 mm	0648 558 060	1
9 mm	160 mm	100 mm	0648 559 016	2
9,5 mm	360 mm	300 mm	0648 559 536	1
10 mm	110 mm	50 mm	0648 551 011	2/10
10 mm	160 mm	100 mm	0648 551 016	2/10/50
10 mm	210 mm	150 mm	0648 551 021	2/10
10 mm	260 mm	200 mm	0648 551 026	2/10
10 mm	310 mm	250 mm	0648 551 031	2/10
10 mm	350 mm	290 mm	0648 551 035	1
10 mm	450 mm	390 mm	0648 551 045	1
10 mm	600 mm	540 mm	0648 551 060	1
10 mm	800 mm	740 mm	0648 551 080	1
10 mm	1000 mm	940 mm	0648 551 010	1
11 mm	210 mm	160 mm	0648 551 121	2
12 mm	160 mm	110 mm	0648 551 216	2/10
12 mm	210 mm	160 mm	0648 551 221	2/10
12 mm	260 mm	210 mm	0648 551 226	2/10
12 mm	310 mm	260 mm	0648 551 231	1
12 mm	360 mm	310 mm	0648 551 236	1
12 mm	450 mm	400 mm	0648 551 245	1
12 mm	600 mm	550 mm	0648 551 260	1
12 mm	1000 mm	950 mm	0648 551 210	1
13 mm	260 mm	210 mm	0648 551 326	1
14 mm	160 mm	110 mm	0648 551 416	2/10
14 mm	210 mm	160 mm	0648 551 421	2/10
14 mm	260 mm	210 mm	0648 551 426	1
14 mm	310 mm	260 mm	0648 551 431	1
14 mm	450 mm	400 mm	0648 551 445	1
14 mm	600 mm	550 mm	0648 551 460	1
14 mm	1000 mm	950 mm	0648 551 410	1
15 mm	160 mm	110 mm	0648 551 516	1
15 mm	210 mm	160 mm	0648 551 521	1
15 mm	260 mm	210 mm	0648 551 526	1
15 mm	450 mm	400 mm	0648 551 545	1
16 mm	160 mm	110 mm	0648 551 616	1
16 mm	210 mm	160 mm	0648 551 621	1
16 mm	260 mm	210 mm	0648 551 626	1
16 mm	310 mm	260 mm	0648 551 631	1
16 mm	450 mm	400 mm	0648 551 645	1