



Komple Set

M5 / M6 / M8 / M10 / M12

- Metrik diş.
- Burç ve takımlar, 5 boyut için, her birinde 2 burç uzunluğu

Art.-Nr. 0964 961 7

Diş Ø x adım x uzunluk mm		Set
M 5 x 0,8 x 7,6	M 8 x 1,25 x 16,2	5
M 5 x 0,8 x 10,0	M 10 x 1,5 x 14,0	
M 6 x 1,0 x 9,4	M 10 x 1,5 x 20,0	
M 6 x 1,0 x 12,0	M 12 x 1,75 x 16,2	
M 8 x 1,25 x 11,7	M 12 x 1,75 x 24,0	

Komple Set

M6 / M8 / M10

- Metrik diş.
- Burç ve takımlar, 3 boyut için, her birinde 2 burç uzunluğu

Art.-Nr. 0964 961 6

Diş Ø x adım x uzunluk mm		Set
M 6 x 1,0 x 9,4	M 8 x 1,25 x 16,2	5
M 6 x 1,0 x 12,0	M 10 x 1,5 x 14,0	
M 8 x 1,25 x 11,7	M 10 x 1,5 x 20,0	

Yedek Burçlar

Model: Çelik, galvanizli pasivize edilmiş ve her biri 25 adet içerikli A2

Diş Ø x adım x uzunluk mm	Art.-Nr. Çelik galvanizli
M 4 x 0,7 x 6,0	0663 4 60*
M 4 x 0,7 x 8,0	0663 4 80*
M 5 x 0,8 x 7,6	0663 5 76
M 5 x 0,8 x 10,0	0663 5 100
M 6 x 1 x 9,4	0663 6 94
M 6 x 1 x 12,0	0663 6 120
M 7 x 1 x 10,0	0663 7 100
M 7 x 1 x 14,0	0663 7 140
M 8 x 1 x 11,7	0663 8 117
M 8 x 1,25 x 11,7	0663 812 511
M 8 x 1,25 x 16,2	0663 812 516
M 10 x 1 x 6,2	0663 101
M 10 x 1 x 9,0	0663 101 90*
M 10 x 1 x 15,0	0663 10 150
M 10 x 1,25 x 9,0	0663 101 250*
M 10 x 1,25 x 15,0	0663 101 251
M 10 x 1,25 x 20,0	0663 101 252
M 10 x 1,5 x 14,0	0663 101 514
M 10 x 1,5 x 20,0	0663 101 520
M 11 x 1,25 x 22,0	0663 111 122*
M 11 x 1,5 x 16,0	0663 111 516*
M 11 x 1,5 x 22,0	0663 111 522*

Metrik diş
Metrik ince diş

Diş Ø x adım x uzunluk mm	Art.-Nr. Çelik galvanizli
M 12 x 1,5 x 6,7	0663 121 567
M 12 x 1,5 x 9,3	0663 121 593
M 12 x 1,5 x 16,3	0663 121 516
M 12 x 1,5 x 24,0	0663 121 524
M 12 x 1,75 x 16,2	0663 121 751
M 12 x 1,75 x 24,0	0663 121 752
M 14 x 1,5 x 6,5	0663 141 565
M 14 x 1,5 x 9,3	0663 141 593
M 14 x 1,5 x 12,8	0663 141 512
M 14 x 1,5 x 16,0	0663 141 516
M 14 x 1,5 x 26,0	0663 141 526
M 16 x 1,5 x 7,0	0663 161 570*
M 16 x 1,5 x 12,7	0663 161 512*
M 16 x 1,5 x 24,0	0663 161 524*
M 16 x 2 x 24,0	0663 16 240*
M 16 x 2 x 32,0	0663 16 320*
M 18 x 1,5 x 10,0	0663 181 610*
M 18 x 1,5 x 18,3	0663 181 518*
M 18 x 1,5 x 27,0	0663 181 527*

* ORSY

Diş Ø x adım x uzunluk mm	Art.-Nr. A2
M 6 x 1 x 9,4	0663 06 94*
M 6 x 1 x 12,0	0663 06 120*
M 8 x 1,25 x 11,7	0663 081 211*
M 8 x 1,25 x 16,2	0663 081 216*
M 10 x 1,5 x 14,0	0663 011 514*
M 10 x 1,5 x 20,0	0663 011 520*

