



## Küresel Uçlu Tornavida

Şaft: Altı köşeli uç, mat kromajlı.  
Kafa tipi: SW, DIN 911 gibi  
Black Point.

mm	A mm	B/C mm	A inç	Art.-Nr.	
2,0	100	83/27	4"	0613 415 02	1
2,5	100	83/27	4"	0613 415 025	
3,0	100	83/27	4"	0613 415 03	
4,0	100	96/31	4"	0613 415 04	
5,0	100	106/35	4"	0613 415 05	
6,0	125	106/35	5"	0613 415 06	
8,0	150	114/38	6"	0613 415 08	
10,0	150	114/38	6"	0613 415 10	
12,0	150	114/38	6"	0613 415 12	



## Tornavida Takımı

İç altı köşe tornavida, küresel başlı

Art.-Nr. 0613 915 6

mm	A mm	Art.-Nr.	mm	A mm	Art.-Nr.	
2,5	100	0613 415 025	5	100	0613 415 05	1
3	100	0613 415 03	6	125	0613 415 06	
4	100	0613 415 04	8	150	0613 415 08	



## Dıştan Altıgen Civatalar İçin Lokma Anahtar

Şaft: Yuvarlak uç, mat kromajlı.  
Kafa tipi: DIN 475/2.  
Standart: DIN 3125.

mm	A mm	B/C mm	A inç	Art.-Nr.	
4,0	125	96/31	5"	0613 436 04	1
4,5	125	96/31	5"	0613 436 045	
5,0	125	96/31	5"	0613 436 05	
5,5	125	96/31	5"	0613 436 055	
6,0	125	96/31	5"	0613 436 06	
7,0	125	106/35	5"	0613 436 07	
8,0	125	106/35	5"	0613 436 08	
9,0	125	106/35	5"	0613 436 09	
10,0	125	106/35	5"	0613 436 10	
11,0	125	114/38	5"	0613 436 11	
12,0	125	114/38	5"	0613 436 12	
13,0	125	114/38	5"	0613 436 13	
14,0	125	120/40,5	5"	0613 436 14	
16,0	125	120/40,5	5"	0613 436 16	
17,0	125	120/40,5	5"	0613 436 17	



## Tornavida Takımı

Dıştan altıgen civata için lokma anahtar tornavida

Art.-Nr. 0613 936 6

mm	A mm	Art.-Nr.	mm	A mm	Art.-Nr.	
6,0	125	0613 436 06	10	125	0613 436 10	1
7,0	125	0613 436 07	12	125	0613 436 12	
8,0	125	0613 436 08	13	125	0613 436 13	