

1/2" LOKMA ANAHTAR ÇEŞİTLERİ



6 köşe

Sıkma mukavemetli sert köpük altlığı

Art.-Nr. 0955 13 230

Metal kutu 405x160x50 mm, Boyut 3

Art.-Nr. 0955 715 3

İçerik: 23 parça

1 Cırcır kol, 1 Uzatma 125 mm,

1 Uzatma 250 mm, 1 Mafsal,

19 Lokma

Anahtar ölçüsü 10, 11, 12, 13, 14, 15, 16, 17,

18, 19, 20, 21, 22, 24, 26, 27, 28, 30, 32

Art.-Nr. 0965 13 230



6 köşe

Sıkma mukavemetli sert köpük altlığı

Art.-Nr. 0955 13 170

Metal kutu 405x160x50 mm, Boyut 3

Art.-Nr. 0955 715 3

İçerik: 17 parça

1 Cırcır kol, 1 Uzatma 125 mm,

1 Uzatma 250 mm, 1 Mafsal,

13 Lokma

Anahtar ölçüsü 10, 11, 12, 13, 14, 15, 17, 19,

22, 24, 27, 30, 32

Art.-Nr. 0965 13 170



12 köşe

Sıkma mukavemetli sert köpük altlığı

Art.-Nr. 0955 13 20

Metal kutu 405x160x50 mm, Boyut 3

Art.-Nr. 0955 715 3

İçerik: 21 parça

1 Cırcır kol, 1 Uzatma 125 mm,

1 Uzatma 250 mm, 1 Mafsal,

1 T-kolu

16 Lokma

Anahtar ölçüsü 10, 11, 12, 13, 14, 15, 16, 17,

18, 19, 22, 24, 27, 30, 32, 34

Art.-Nr. 0965 13 20



inç

Sıkma mukavemetli sert köpük altlığı

Art.-Nr. 0955 13 21

Metal kutu 405x160x50 mm, Boyut 3

Art.-Nr. 0955 715 3

İçerik: 21 parça

1 Cırcır kol, 1 Uzatma 125 mm

1 Uzatma 250 mm, 1 Mafsal,

17 Lokma

Anahtar ölçüsü 3/8; 7/16; 1/2; 9/16; 19/32;

5/8; 11/16; 3/4; 25/32; 13/16; 7/8; 15/16;

1 1/16; 1 1/8; 1 3/16; 1 1/4

Art.-Nr. 0965 13 21