

PNEUMATIC RIVET NUT UNIT



Attention: Thread mandrels and mouthpieces not included in delivery.

Delivery Scope		
Designation	Art. No.	P. Qty.
PEG 312	0703 937 55	1
Operating instructions	-	1

Suitable Accessories		
Designation	Art. No.	P. Qty.
Mouthpiece M3	0948 937 30	1
Mouthpiece M4	0948 937 40	1
Mouthpiece M5	0948 937 50	1
Mouthpiece M6	0948 937 60	1
Mouthpiece M8	0948 937 80	1
Mouthpiece M10	0948 937 100	1
Mouthpiece M12	0948 937 120	1
Thread mandrel M3	0948 937 3	1
Thread mandrel M4	0948 937 4	1
Thread mandrel M5	0948 937 5	1
Thread mandrel M6	0948 937 6	1
Thread mandrel M8	0948 937 8	1
Thread mandrel M10	0948 937 10	1
Thread mandrel M12	0948 937 12	1
Plug-in nipple (brass) 1/4"	0699 211 4	1
Compr.-air hose, inner dia. 6 mm, 10 m	0699 906 1	1

The smallest, most lightweight pneumatic rivet nut unit for the fast and easy processing of rivet nuts made of aluminum, steel, and stainless steel in the dimensions dia. M3 - M12.

PEG 312

Art. No. 0703 937 55

- Toolless quick-changing system for thread mandrels.
- Stainless steel rivet nuts, processible up to M10.
- Simple stroke setting due to readable strokescale.
- Low weight due to lightweight construction.
- Automatic twist-in/twist-out system for rivet nuts.
- Suspension hook for stationary use.
- Deactivatable air connection.
- Additional twist-out button on the back of the housing.
- Adjustable air connection 360°.
- 3 year warranty.

Technical Data	
Weight	1.6 kg
Dimensions	280 x 260 x 85 mm
Operating pressure	max. 7 bar
Setting force	18,500 N
Device stroke	7 mm
Air consumption	1.5 liters
Hose connection	1/4"
Noise emission	85 dB