

Malleable-Iron Screw Clamp

For rigid, non-elastic, secure clamping.

- Fixed and sliding bar made of high-quality, powder-coated, malleable cast iron (pos. 1).
→ **High stability and improved corrosion protection.**
- Movable, cold-extruded pressure plate, electrogalvanised (pos. 2).
- With slip prevention, whereby a threaded pin engages in the track guide (pos. 3)
→ **Greatest safety! No slipping or loosening.**
- Hollow profile track made of cold-drawn quality steel, with six grooves, electrogalvanized (pos. 4).
→ **High stability and good corrosion protection.**
- Spindle with trapezoidal thread, rolled and strain-hardened (pos. 5)
→ **Extreme anti-wearing and very smooth running.**
- With protective caps (pos. 6).

| L in mm | L 1 in mm | W in mm | L 2 in mm | Art. No. | |
|------------|--------------|------------|--------------|--------------|---|
| 120 | 60 | 20 | 5 | 0714 671 12 | 1 |
| 160 | 80 | 25 | 6 | 0714 671 16 | |
| 200 | 100 | 27 | 7 | 0714 671 20 | |
| 250 | 100 | 27 | 7 | 0714 672 25 | |
| 250 | 120 | 29 | 9 | 0714 671 25 | |
| 300 | 120 | 29 | 9 | 0714 672 30 | |
| 400 | 120 | 29 | 9 | 0714 672 40 | |
| 500 | 120 | 29 | 9 | 0714 671 500 | |
| 600 | 120 | 29 | 9 | 0714 671 600 | |
| 800 | 120 | 29 | 9 | 0714 671 800 | |
| 1000 | 120 | 29 | 9 | 0714 671 101 | |
| 300 | 140 | 32 | 10 | 0714 671 30 | |
| 500 | 140 | 32 | 10 | 0714 672 50 | |
| 600 | 140 | 32 | 10 | 0714 672 60 | |

- Stable design (screw clamps) without protective caps.

| L in mm | L 1 in mm | W in mm | L 2 in mm | Art. No. | |
|------------|--------------|------------|--------------|--------------|---|
| 500 | | | | 0714 671 50 | 1 |
| 600 | | | | 0714 671 60 | |
| 800 | | | | 0714 671 80 | |
| 1000 | | | | 0714 671 100 | |
| 1250 | 120 | 35 | 11 | 0714 671 125 | |
| 1500 | | | | 0714 671 150 | |
| 1800 | | | | 0714 671 180 | |
| 2000 | | | | 0714 671 200 | |
| 2200 | | | | 0714 671 220 | |
| 2500 | | | | 0714 671 250 | |

Protective Cap Strips

For all conventional screw clamps for careful clamping

- Can be tightened on both sides and cut as required.

Art. No. 0714 67 102
2 pieces in a polybag



Just slip on the protective cap strips and cut them as required.

