

HOSE CLAMP WITH CLAMPING JAW



For connections with high and even contact pressure

Powerful clamping jaw design

- High clamping force
- High density



Material	Steel
Surface	Galvanised
Norms	DIN 3017
RoHS-compliant	Yes

Width of band	Nominal diameter	Drive type	Width across flats	Tightening torque	Art. No.	P. Qty.
7 mm	8 mm	Slot		0.5 Nm	0540 8 7	25
9 mm	9 mm	Slot		1.2 Nm	0540 9 9	25
9 mm	10 mm	Slot		1.2 Nm	0540 10 9	25
9 mm	11 mm	Slot		1.2 Nm	0540 11 9	25
9 mm	12 mm	Slot		1.2 Nm	0540 12 9	25
9 mm	13 mm	Slot		1.2 Nm	0540 13 9	25
9 mm	14 mm	Slot		1.2 Nm	0540 14 9	25
9 mm	15 mm	Slot		1.2 Nm	0540 15 9	25
9 mm	16 mm	Slot		1.2 Nm	0540 16 9	25
9 mm	17 mm	Slot		1.2 Nm	0540 17 9	25
9 mm	18 mm	Slot		1.2 Nm	0540 18 9	25
9 mm	19 mm	Slot		1.2 Nm	0540 19 9	50
9 mm	20 mm	Slot		1.2 Nm	0540 20 9	50
9 mm	22 mm	Slot		1.2 Nm	0540 22 9	25
12 mm	17 mm	Slot/hexagon	8 mm	1.5 Nm	0540 17 12	25
12 mm	18 mm	Slot/hexagon	8 mm	1.5 Nm	0540 18 12	25
12 mm	19 mm	Slot/hexagon	8 mm	1.5 Nm	0540 19 12	25
15 mm	25 mm	Slot/hexagon	10 mm	4.0 Nm	0540 25 15	25

Application area

Airbag, clamping/fastening