

1/4" + 1/2" SOCKET WRENCH ASSORTMENT, DUST-PROTECTED

| Scope of delivery for Art. No. | Designation | Art. No. | Number |
|-----------------------------------|---|---------------------|--------|
| 0965 090 590 | 1/2" lever reversible ratchet, dust protected | 0712 012 03 | 1 |
| | 1/2" socket wrench insert 10 mm | 0712 131 110 | 1 |
| | 1/2" socket wrench insert 11 mm | 0712 131 111 | 1 |
| | 1/2" socket wrench insert 12 mm | 0712 131 112 | 1 |
| | 1/2" socket wrench insert 13 mm | 0712 131 113 | 1 |
| | 1/2" socket wrench insert 14 mm | 0712 131 114 | 1 |
| | 1/2" socket wrench insert 15 mm | 0712 131 115 | 1 |
| | 1/2" socket wrench insert 16 mm | 0712 131 116 | 1 |
| | 1/2" socket wrench insert 17 mm | 0712 131 117 | 1 |
| | 1/2" socket wrench insert 18 mm | 0712 131 118 | 1 |
| | 1/2" socket wrench insert 19 mm | 0712 131 119 | 1 |
| | 1/2" socket wrench insert 20 mm | 0712 131 120 | 1 |
| | 1/2" socket wrench insert 21 mm | 0712 131 121 | 1 |
| | 1/2" socket wrench insert 22 mm | 0712 131 122 | 1 |
| | 1/2" socket wrench insert 24 mm | 0712 131 124 | 1 |
| | 1/2" socket wrench insert 26 mm | 0712 131 126 | 1 |
| | 1/2" socket wrench insert 27 mm | 0712 131 127 | 1 |
| | 1/2" socket wrench insert 28 mm | 0712 131 128 | 1 |
| | 1/2" socket wrench insert 30 mm | 0712 131 130 | 1 |
| | 1/2" socket wrench insert 32 mm | 0712 131 132 | 1 |
| | 1/2" angled extension 50 mm | 0712 138 100 | 1 |
| | 1/2" extension 125 mm | 0712 138 105 | 1 |
| | 1/2" extension 250 mm | 0712 138 110 | 1 |
| | 1/2" cardan joint | 0712 138 301 | 1 |
| | Slotted bit 0.8 x 5.5 mm | 0614 175 653 | 1 |
| | Phillips bit PH1 | 0614 176 274 | 1 |
| | Phillips bit PH2 | 0614 176 461 | 1 |
| | Phillips bit PH3 | 0614 176 648 | 1 |
| | Hexagon socket bit 3 mm | 0614 176 93 | 1 |
| | Hexagon socket bit 4 mm | 0614 176 94 | 1 |
| | Hexagon socket bit 5 mm | 0614 176 95 | 1 |
| | Hexagon socket bit 6 mm | 0614 176 96 | 1 |
| | TX bit 10 | 0614 311 0 | 1 |
| | TX bit 15 | 0614 31 15 | 1 |
| | TX bit 20 | 0614 31 20 | 1 |
| | TX bit 25 | 0614 31 25 | 1 |
| | TX bit 27 | 0614 31 27 | 1 |
| | TX bit 30 | 0614 31 30 | 1 |
| | TX bit 40 | 0614 314 0 | |