

Brake cleaner

For cleaning and degreasing during maintenance and repair work

Fast flash-off behaviour and excellent cleaning performance

- Fast and effective removal of soot, grease, brake dust and oily residues
- Residue-free cleaning

Acetone-free

Good material compatibility with paints, plastics, seals and rubber

AOX-free and silicone-free

Chemical basis	Naphtha
Shelf life from production	24 Month



Illustration only

Contents	Container	Smell/fragrance	Art. no.	P. Qty.
500 ml	Aerosol can	Solvent-like	0890 108 7	1/24
5 l	Canister	Characteristic	0890 108 715	1
20 l	Canister	Characteristic	0890 108 716	1
20 l	Canister	Characteristic	0890 108 720	1
60 l	Barrel	Characteristic	0890 108 760	1

Details/Application

For quickly removing oily/greasy residues, soot, brake dust on vehicles, disc and drum brakes, engine and gearbox housings etc.

Instructions

Spray the surfaces to be cleaned and wipe with a clean cloth. Repeat the process for heavy soiling.

Notice

Do not spray on hot parts. Not suitable for surface cleaning of adhesive areas. Prior to application, the compatibility of rubber or plastic parts and painted surfaces should be checked on an area that is not visible.

The usage instructions are recommendations based on the tests we have conducted and our experience; carry out your own tests before each application. Due to the large number of applications and storage and processing conditions, we do not assume any liability for a specific application result. Insofar as our free customer service provides technical information or acts as an advisory service, no responsibility is assumed by this service except where the advice or information given falls within the scope of our specified, contractually agreed service or the advisor was acting deliberately. We guarantee consistent quality of our products. We reserve the right to make technical changes and further develop products.

Related products for	Designation	Art. no.
0890 108 715	Product-specific pressure sprayer, unfilled	0891 503 002
	Filling system REFILLO®	0891 800 1
	Tap DN 45 thread For 5 l and 10 l plastic canisters Tap for 5 l and 10 l plastic canisters with a DN 45 thread	0891 302 01
	Compressed-air filling station Refillo® combi	0891 800 001
0890 108 716	Product-specific pressure sprayer, unfilled	0891 503 002
	Plastic tap DN 60 connection For plastic canisters with DN 60 connection for 20 L/25 L and 60 L	0891 302 03
	Canister coating ORSY®protec	0891 870 77
0890 108 720	Filling system REFILLO®	0891 800 1
	Canister coating ORSY®protec	0891 870 77
0890 108 760	Product-specific pressure sprayer, unfilled	0891 503 002
	REFILLO®mat filling can	0891 881 1
	REFILLOmat filling system	0961 891 011