

Twist Drill bit assortment DIN 338 HSS

Assembly drill for general, broad applications in steel up to 850 N/mm² strength and cast iron.

Quick drilling

- Web thinning ensure less friction during drilling and therefore less feed force needed.
- The optimized point grinding with short designed working length enable quick drilling by using cordless and wired drill at construction site and in assembly

Self-centering


The crosswise grinding ensures an excellent centering effect even on domed surfaces, eliminating the need for center-punching or piloting

Contents:

- 19 pcs
- Ø 1,0 - 10,0 x 0.5 mm



●●○○



●●○○



●○○○

Details/Application

Steel