

Hexagonal bolt with thread up to head assortment

350 pieces in system case 4.4.1. ISO 4017, 8.8 zinc-plated steel, blue passivated (A2K)


Standards	ISO 4017
Material	Steel
Property class	8.8
Surface	Zinc plated
Number of pieces in assortment/set	333 PCS
Product weight (per item)	9763 g



Art. No. 5964 005 702

P. Qty.: 1

ORSY



Notice

ISO 4017 replaces DIN 933 | There is some similarity | Nominal dimensions extended | Width across flats changed for M10, M12, M14 and M22.

Contents for Art. No. 5964 005 702

Designation	Art. No.	Quantity
Hexagonal bolt with thread up to the head M8 x 16 mm	0057 8 16	50
Hexagonal bolt with thread up to the head M8 x 20 mm	0057 8 20	50
Hexagonal bolt with thread up to the head M8 x 25 mm	0057 8 25	40
Hexagonal bolt with thread up to the head M8 x 30 mm	0057 8 30	40
Hexagonal bolt with thread up to the head M10 x 20 mm	0057 910 20	25
Hexagonal bolt with thread up to the head M10 x 25 mm	0057 910 25	25
Hexagonal bolt with thread up to the head M10 x 30 mm	0057 910 30	20
Hexagonal bolt with thread up to the head M10 x 40 mm	0057 910 40	20
Hexagonal bolt with thread up to the head M12 x 30 mm	0057 912 30	20
Hexagonal bolt with thread up to the head M12 x 35 mm	0057 912 35	15
Hexagonal bolt with thread up to the head M12 x 40 mm	0057 912 40	15
Hexagonal bolt with thread up to the head M12 x 50 mm	0057 912 50	13
System insert, plastic, 4.4.1 12-fach	5581 003 003	1
System case 4.4.1		1