

Standard cable connector with plastic latch

For quick, problem-free and reliable bundling of cables, cable harnesses, hoses etc.

Good recycling properties

Secure grip on bundled cables

Inner toothing on tie

No additional assembly tools required

Can be attached by hand

Resistant to bases, oils, greases and motor vehicle fuels



Illustration only

| | |
|----------------------------------|----------------|
| Material | PA - Polyamide |
| Min./max. temperature resistance | -40 to 85 °C |
| Min./max. processing temperature | -10 to 85 °C |
| Silicone-free | Yes |
| Halogen-free | Yes |

| Colour | Width | Length | Min./max. bundle diameter (Bündel-Ø min./max.) | Art. no. | P. Qty. |
|---------|---------|---------|--|-------------------|---------------|
| Black | 2.5 mm | 100 mm | 1.6-20 mm | 0502 111 | 100/300 /1000 |
| Black | 3.6 mm | 140 mm | 1.6-30 mm | 0502 121 | 100/300 /1000 |
| Black | 3.6 mm | 200 mm | 1.6-40 mm | 0502 131 | 100/1000 |
| Black | 3.6 mm | 280 mm | 1.6-75 mm | 0502 135 1 | 100/500 |
| Black | 4.8 mm | 178 mm | 1.6-40 mm | 0502 141 | 100/300 /1000 |
| Black | 4.8 mm | 250 mm | 4-68 mm | 0502 141 4 | 100 |
| Black | 4.8 mm | 280 mm | 1.6-75 mm | 0502 151 | 100/300 |
| Black | 4.8 mm | 360 mm | 1.6-100 mm | 0502 161 | 100/300 |
| Black | 7.8 mm | 180 mm | 1.6-40 mm | 0502 171 | 100/300 |
| Black | 7.8 mm | 300 mm | 5-76 mm | 0502 171 3 | 100 |
| Black | 7.8 mm | 360 mm | 1.6-100 mm | 0502 181 | 100 |
| Black | 7.8 mm | 540 mm | 25-150 mm | 0502 190 1 | 100 |
| Black | 7.8 mm | 750 mm | 40-220 mm | 0502 181 3 | 100 |
| Black | 12.5 mm | 720 mm | 48-220 mm | 0502 201 1 | 50 |
| Black | 12.5 mm | 1000 mm | 48-300 mm | 0502 202 2 | 50 |
| Natural | 2.5 mm | 100 mm | 1.6-20 mm | 0502 11 | 100/1000 |
| Natural | 2.5 mm | 200 mm | 1-52 mm | 0502 115 | 1000 |
| Natural | 3.6 mm | 140 mm | 1.6-30 mm | 0502 12 | 100/1000 |
| Natural | 3.6 mm | 200 mm | 1.6-40 mm | 0502 13 | 100/1000 |
| Natural | 3.6 mm | 280 mm | 1.6-75 mm | 0502 135 | 100/500 |
| Natural | 4.8 mm | 178 mm | 1.6-40 mm | 0502 14 | 100/1000 |
| Natural | 4.8 mm | 250 mm | 4-68 mm | 0502 14 4 | 100 |
| Natural | 4.8 mm | 280 mm | 1.6-75 mm | 0502 15 | 100 |
| Natural | 4.8 mm | 360 mm | 1.6-100 mm | 0502 16 | 100 |
| Natural | 7.8 mm | 180 mm | 1.6-40 mm | 0502 17 | 100 |

| Colour | Width | Length | Min./max. bundle diameter (Bündel-Ø min./max.) | Art. no. | P. Qty. |
|---------|---------|---------|--|--------------------|---------|
| Natural | 7.8 mm | 360 mm | 1.6-100 mm | 0502 18 | 100 |
| Natural | 7.8 mm | 540 mm | 25-150 mm | 0502 19 | 100 |
| Natural | 7.8 mm | 750 mm | 40-220 mm | 0502 181 31 | 100 |
| Natural | 12.5 mm | 720 mm | 48-220 mm | 0502 201 | 50 |
| Natural | 12.5 mm | 1000 mm | 48-300 mm | 0502 202 | 50 |

Details/Application

Control cabinet construction, installations, motor vehicle construction, motor vehicle workshops, factory workshops, elevator construction

Natural: For indoor use

Black: UV- and weather-stabilized. Carbon additives slow down the effect of UV light on the material.



Notice

Exercise caution with strong mineral acids and/or oxidising chemicals, especially at high temperatures
Not resistant to mineral acids and/or oxidising chemicals.

| Related products for | Designation | Art. no. |
|----------------------|---|---------------------|
| 0502 131 | Cable ties KBL 2 black with plastic latch | 0502 000 131 |
| 0502 141 | Cable ties KBL 2 black with plastic latch | 0502 000 141 |
| 0502 151 | Cable ties KBL 2 black with plastic latch | 0502 000 151 |
| 0502 161 | Cable ties KBL 2 black with plastic latch | 0502 000 161 |
| 0502 181 | Cable ties KBL 2 black with plastic latch | 0502 000 181 |