

Pneumatic impact screwdriver DSS 1/2 inch H



Reliable, powerful impact screwdriver with fast build-up of torque

Perfect weight distribution

Rugged, well-balanced unit in aluminium housing

Very handy and user-friendly

Rubberised and ergonomically designed handle, user-friendly right/left changeover and adjustable trigger

Long service life and virtually vibration-free

High-quality pin impact mechanism in oil bath with 6-disc motor.

2 Years WÜRTH MASTERPLUS Warranty for wear damage

The current WÜRTH MASTERPLUS warranty conditions must be observed.

3 Years Warranty on manufacturing and material defects

Excluded are damages caused by improper use, overloading or failure to observe the operating instructions.

Art. no. 0703 736 0

P. Qty.: 1

Individually boxed

Type description	DSS 1/2 inch H
Tool holding device	1/2-inch external square
Max. working torque	470 Nm
Max. releasing torque	569 Nm
Sound-pressure level	92 dB
Vibration	3.78 m/s ²
Working pressure	6.3 bar
Weight of machine	2.3 kg
Min. hose inner diameter	8 mm
Air consumption	102 l/min
Connection thread	1/4 inch
Length x width x height	195 x 64 x 202 mm

Level	Tightening torques Nm (approx. values)	Releasing torque Nm
1	70	Max. 569
2	120	
3	280	
4	470	

Details/Application



The control piston as well as the four tightening torque stages can be operated one-handed and enable optimum adjustment for the respective application.

Notice

- Recommended maximum bolt size: M15
- Impact screwdrivers are not torque screwdrivers. Connections requiring a specific torque must be checked by means of a torque measuring device after tightening with the impact screwdriver.
- The operating torque is the torque usually achieved under average working conditions. It is dependent on the highly varying ambient conditions (air pressure, hose diameter, soiling etc.).
- When used regularly, the machine should be lightly oiled via the pneumatic air supply every day. The use of a mist lubricator is recommended

Plug-in nipple not included in scope of delivery

Related products	Art. no.
Pressure reducing valve	0699 003 60
Small mist lubricator	0699 070 314
Plug-in nipple S2000 MT	0699 100 614
Special oil 1 l	0893 050 5