

Pneumatic impact screwdriver DSS 1/2" Standard



High-quality impact screwdriver in robust, aluminum alloy housing, with best performance in its class

Outstanding power-to-weight ratio

Up to 860 Nm of maximum torque in reverse due to the high performance twin hammer impact mechanism.

6-stage power setting position with convenient one-handed switchover in forward & reverse

Optimum, user-friendly adjustment to respective application.

Comfortable handling with Ergonomic grip

Rubber-coated and ergonomically shaped handle, balanced center of gravity position and handling

Handle exhaust

Directs the air away from operator and work area

Details/Application

Perfectly suitable for wheel changes on passenger cars.

Notice

- Recommended maximum bolt size: M16
- Impact screwdrivers are not torque screwdrivers. Connections requiring a specific torque must be checked by means of a torque measuring device after tightening with the impact screwdriver.
- The operating torque is the torque usually achieved under average working conditions. It depends on the highly varying ambient conditions (air pressure, hose diameter, soiling etc.).
- When the impact screwdriver is used regularly (e.g. for tyre maintenance), a little oil should be added daily, and approximately 2 strokes of gear grease should be added monthly via the grease nipple.

Plug-in nipple not included in the scope of delivery