


Sandpaper, waterproof

Silicon carbide

- Can be used without soaking, extremely flexible grain carrier
- Sharply contoured working
- Outstanding finish
- Excellent contact with the material and optimum grip
- First-rate initial and long-term grinding performance with a long service life
- Dense scattering



Length x width	280 x 230 mm
Material of abrasive medium	Silicon carbide
Scattering	Close scattering
Adhesive base	Synthetic resin

Grid size	Backing material	Art. no.	P. Qty.
P60	C-weight paper	0584 11 60	50
P80	C-weight paper	0584 11 80	50
P100	C-weight paper	0584 11 100	50
P120	C-weight paper	0584 11 120	50
P150	C-weight paper	0584 11 150	50
P180	B-weight paper	0584 11 180	50
P220	B-weight paper	0584 11 220	50
P240	B-weight paper	0584 11 240	50
P280	B-weight paper	0584 11 280	50
P320	B-weight paper	0584 11 320	50
P360	B-weight paper	0584 11 360	50
P400	B-weight paper	0584 11 400	50
P500	B-weight paper	0584 11 500	50
P600	B-weight paper	0584 11 600	50
P800	B-weight paper	0584 11 800	50
P1000	B-weight paper	0584 111 000	50
P1200	B-weight paper	0584 111 200	50
P2000	B-weight paper	0584 112 000	50

Details/Application

Sanding synthetic resin, nitro and thermoplastic acrylic lacquer structures.

Sanding conventional fillers (P400–P800).

Touching up flaws in the cover coat (P1000–P2000), in case of dust inclusions or dirt particles (P2000).