

Windscreen cutting line

For damage-free removal of vehicle windows with particularly narrow gaps.

High-tech fibres for very high tensile force

Extremely tear-resistant cutting thread for use in tight corners and in particularly narrow gaps

Minimal risk of paint and interior damage

Thanks to its round cross section, cutting injuries are virtually unheard of.

Reusable and flexible

- Can be used 2-4 times
- If the thread tears, it can be knotted to continue working



Form	Roll
Material	PE - Polyethylene

Min. tensile force	Length	Colour	Cord thickness	Art. no.	P. Qty.
1600 N	65 m	Orange	0.8 mm	0714 58 284	1
1800 N	25 m	Red	0.85 mm	0714 58 283	1
1850 N	65 m	Red	1.1 mm	0714 58 240	1

Notice

The tensile strength is specified in N in this case; for cutting wires, it is indicated in N/mm². One square cutting wire with 0.6 x 0.6 mm cross section and 2000 N/mm² corresponds to tensile strength of approx. 720 N.

Related products	Art. no.
Wire feeder	0714 58 213