

Rechargeable LED Head lamp Ergopower Sensor

Strong light beam headlamp enables hands free professional operation of tools and machines thanks to sensor switch and high capacity battery

Super bright light emitting surface 60 degree lighting

Adjustable back bracket up and down with in 60 degrees

Equipped with two switches:

- Standard on/off switch - 1. step half light intensity, 2. step full light intensity
- Sensor switch - Motion sensor (with hand movements) up to 5 cm distance to the lamp

Protection class IP65

Impact resistance IK07

Headband with integrated anti-slip rubber strip

Provides a better grip



IP65

Details/Application



Notice

Supplied with Micro-USB