

VDE cable shears with dual blade

For cutting copper and aluminium cable; for pre-cutting and recutting

- For working on live parts up to 1000 volts (AC) and up to 1500 volts (DC), observing all prescribed safety precautions
- High-quality tool steel ensures long tool life and precision of cutting surfaces
- Special blade geometry facilitates easy and distortion-free cutting action through single or multi-stranded cable
- 2-stage operation with dual blades for optimum transmission of forces
- Ergonomic and slip-free 2-component comfort handle with wide VDE collar for safe working
- Cutting: hardened precision blades
- Surface: ground and chrome-plated
- Joint: bolted and adjustable



Length (L)	210 mm
Length in inches (L)	8 in
Max. cable diameter cutting capacity in aluminium/copper	20 mm
Max. aluminium/copper wire cross-section cutting capacity	70 mm ²
EN standard	60900

Art. no. 0714 01 586

P. Qty.: 1 / 10

Details/Application



Details/Application

