

İç Altı Köşe Allen Anahtarı

Şaft: Altı köşeli şaft, parlak nikelajlı, kısa model.
Kafa tipi: ISO 2936 (DIN 911 gibi)



mm	U1 mm	U2 mm	Art.-Nr.	
1,0	45	14	0715 31 59	1/20
1,5	47	16	0715 31 35	
2,0	52	18	0715 31 36	
2,5	59	21	0715 31 37	
3,0	66	23	0715 31 38	
3,5	70	26	0715 31 57	1/10
4,0	74	29	0715 31 39	
4,5	80	31	0715 31 391	
5,0	85	33	0715 31 40	
5,5	90	35	0715 31 401	
6,0	96	38	0715 31 41	1
7,0	102	41	0715 31 42	
8,0	108	44	0715 31 43	
9,0	114	47	0715 31 44	
10,0	122	50	0715 31 45	
11,0	129	53	0715 31 46	1
12,0	137	57	0715 31 47	
14,0	154	70	0715 31 48	
16,0	168	73	0715 31 481	
17,0	177	80	0715 31 49	
19,0	199	89	0715 31 50	1
22,0	222	102	0715 31 51	

Allen anahtar iç altı köşe


Şaft: Altı köşeli şaft, parlak nikelajlı, uzun model.
Kafa tipi: Allen anahtar seti



mm	U1 mm	U2 mm	Art.-Nr.	
2,0	102	18	0715 31 17	1/10
2,5	115	21	0715 31 18	
3,0	129	23	0715 31 19	
3,5	140	26	0715 31 58	
4,0	144	29	0715 31 20	
5,0	165	33	0715 31 21	1/5
6,0	186	38	0715 31 22	
7,0	197	41	0715 31 23	
8,0	208	44	0715 31 24	
9,0	219	47	0715 31 25	
10,0	234	50	0715 31 26	1
12,0	262	57	0715 31 28	
14,0	294	70	0715 31 29	
17,0	337	80	0715 31 30	

Allen anahtar seti

- Plastik tutucu içinde, kısa model.



Set	İçerik mm	Art.-Nr.	
9 par.	1,5, 2, 2,5, 3, 4, 5, 6, 8, 10	0715 31 100	1
10 par.	1,5, 2, 2,5, 3, 4, 6, 8, 10, 12	0715 31 110	
14 par.	2, 3, 4, 5, 6, 7, 8, 9, 10, 11, 12, 14, 17, 19	0715 31 54*	

* Plastik çanta ile sunulur.


- Halkada, kısa model.



Set	İçerik mm	Art.-Nr.	
8 par.	2, 2,5, 3, 4, 5, 6, 8, 10	0715 31 55	1

Allen anahtar seti

- Plastik tutucu içinde, uzun model.



Set	İçerik mm	Art.-Nr.	
9 par.	1,5, 2, 2,5, 3, 4, 5, 6, 8, 10	0715 31 120	1