

Dia. in mm	L in mm	B in mm	H in mm	S in mm	Art. No.	P. Qty.
2.0	11.0	7.0	1.5	0.25	<b>0500 111 85</b>	100
2.5	11.0	7.0	1.5	0.25	<b>0500 111 84</b>	
3.0	12.6	8.0	2.0	0.35	<b>0500 111 41</b>	100/500
3.5	12.6	8.0	2.0	0.35	<b>0500 111 83</b>	100
4.0	14.2	9.5	2.5	0.35	<b>0500 111 82</b>	100/500
4.5	20.0	13.5	2.3	0.50	<b>0500 113 67</b>	100
5.0	15.8	9.5	2.5	0.35	<b>0500 113 55</b>	



Dia. in mm	D <sub>1</sub> in mm	S in mm	H in mm	Art. No.	P. Qty.
2.5	9.5	0.30	1,5	<b>0500 117 53</b>	100/300
5.0	13.0	0.35	1,3	<b>0500 518 36</b>	100




Att. thickness	Att. hole	A	B	C	D	Color	Art. No.	P. Qty.
0.75 - 3.0	5.0 - 5.2	5.0	8.5	2.0	6.0	Black	<b>0500 128 21</b>	25
0.8 - 4.5	3.0 - 3.6	2.9	4.8	1.5	6.0	Black	<b>0500 126 94</b>	50
1.5 - 5.0	5.0 - 5.3	5.0	9.0	2.3	7.5	Black	<b>0500 124 28</b>	
1.5 - 5.0	5.0 - 5.7	5.0	10.0	2.0	7.5	Black	<b>0500 128 54</b>	25
1.6 - 4.5	3.5 - 3.9	3.5	8.0	2.0	7.0	Black	<b>0500 143 00</b>	50
2.0 - 8.0	5.9 - 7.1	5.9	10.0	2.0	12.0	Black	<b>0500 127 10</b>	
2.5 - 5.0	3.8 - 4.0	3.8	8.0	2.0	7.0	Black	<b>0500 124 78</b>	
2.5 - 7.0	5.5 - 6.4	5.5	16.0	2.0	11.0	Black	<b>0501 103 035</b>	25
3.0 - 8.0	5.0 - 5.9	5.0	10.0	2.0	11.4	Neutral	<b>0500 126 96</b>	
3.5 - 6.0	8.0 - 8.2	8.0	18.0	2.5	10.0	Black	<b>0500 148 02</b>	100
4.0 - 7.0	7.9 - 8.5	7.9	16.0	2.0	12.0	Black	<b>0501 101 000</b>	
5.0 - 11.0	5.6 - 6.6	5.6	9.0	2.0	16.0	Black	<b>0500 554 00</b>	50
5.5 - 10.0	8.0 - 8.6	8.0	13.0	3.4	15.5	Black	<b>0501 104 038</b>	
2.0 - 5.6	7.8	7.8	16.0	2.0	10.6	Black	<b>0501 103 015</b>	
6.0 - 11.0	5.0 - 5.5	5.0	10.0	2.0	15.0	Black	<b>0500 491 00</b>	25
7.5 - 8.6	6.0 - 6.2	5.9	16.0	2.5	14.5	Black	<b>0500 141 42</b>	

## Spring Nuts

- Easy to install on smooth bolts, shafts and axes
- The elasticity of the spring nuts ensures that the connection is not affected by vibrations.
- Fast installation by hand.

## Assortments



Contents:  
 12 sheet-metal nut sizes  
 from 2.9 to 8.0 mm = 575 parts.  
 4 spring nut sizes  
 from 2.5 to 4.0 mm = 800 parts.

**Art. No. 0964 500 10**

## Plastic Expanding Rivets

- Plastic expanding rivets are suitable for the quick attachment of sheet metal, cardboard and plastic.
- Their different sizes enable the connection of materials of various thicknesses.
- Applications include the automotive industry and all areas of attachment technology.
- Material: Polyoxymethylene, polyamide 6 or 6.6, 11 or 12, polypropylene, PE.

