



# Hexagon Bolts and Nuts

**UNF / SAE  
UNC / USS**

Steel 8.8 /  $\gamma$  galvanized,  
blue passivated

## Hexagon bolts UNF / SAE

Thread dia. (inches)	1/4"	5/16"	3/8"	7/16"	1/2"	5/8"	3/4"
Size in mm	11.11	12.7	14.29	15.88	19.05	23.81	25.58
Size in inches	7/16	1/2	9/16	5/8	3/4	15/16	1 1/8
No. of threads/inch	28	24	24	20	20	18	16

Thread dia. in inches	Length in inches	Steel 8.8 galv., blue passivated <b>Art. No.</b>	P. Qty.	
1/4	1/2	<b>0071 14 12</b>	100	
	5/8	<b>0071 14 58</b>		
	3/4	<b>0071 14 34</b>		
	7/8	<b>0071 14 78</b>		
	1	<b>0071 14 1</b>	50	
	1 1/4	<b>0071 14 114</b>		
	1 1/2	<b>0071 14 112</b>		
	1 3/4	<b>0071 14 134</b>		
	2	<b>0071 14 2</b>		
2 1/2	<b>0071 14 212</b>	25		
5/16	1/2		<b>0071 516 12</b>	
	5/8		<b>0071 516 58</b>	
	3/4		<b>0071 516 34</b>	
	7/8		<b>0071 516 78</b>	
	1		<b>0071 516 1</b>	
	1 1/4		<b>0071 516 114</b>	
	1 1/2		<b>0071 516 112</b>	
	1 3/4		<b>0071 516 134</b>	
	2	<b>0071 516 2</b>		
2 1/4	<b>0071 516 214</b>	25		
2 1/2	<b>0071 516 212</b>			
2 3/4	<b>0071 516 234</b>			
3	<b>0071 516 3</b>			
3/8	5/8		<b>0071 38 58</b>	25
	3/4		<b>0071 38 34</b>	
	7/8		<b>0071 38 78</b>	
	1		<b>0071 38 1</b>	25
	1 1/4		<b>0071 38 114</b>	
	1 1/2	<b>0071 38 112</b>		
	1 3/4	<b>0071 38 134</b>		
	2	<b>0071 38 2</b>		
	2 1/2	<b>0071 38 212</b>		

Thread dia. in inches	Length in inches	Steel 8.8 galv., blue passivated <b>Art. No.</b>	P. Qty.
3/8	2 1/4	<b>0071 38 214</b>	25
	2 1/2	<b>0071 38 212</b>	
	2 3/4	<b>0071 38 234</b>	
	3	<b>0071 38 3</b>	
7/16	3/4	<b>0071 716 34</b>	25
	1	<b>0071 716 1</b>	
	1 1/4	<b>0071 716 114</b>	
	1 1/2	<b>0071 716 112</b>	
	1 3/4	<b>0071 716 134</b>	
	2	<b>0071 716 2</b>	
1/2	3/4	<b>0071 12 34</b>	25
	1	<b>0071 12 1</b>	
	1 1/4	<b>0071 12 114</b>	
	1 1/2	<b>0071 12 112</b>	
	1 3/4	<b>0071 12 134</b>	
	2	<b>0071 12 2</b>	
	2 1/4	<b>0071 12 214</b>	
	2 1/2	<b>0071 12 212</b>	
	2 3/4	<b>0071 12 234</b>	
	3	<b>0071 12 3</b>	
3 1/4	<b>0071 12 314</b>	25	
3 1/2	<b>0071 12 312</b>		
5/8	2 <b>0071 58 2</b>		
2 1/2	<b>0071 58 212</b>		
3/4	4	<b>0071 58 4</b>	25
	2	<b>0071 34 2</b>	
	2 1/4	<b>0071 34 214</b>	25
	3	<b>0071 34 3</b>	
	3 1/4	<b>0071 34 314</b>	
	4	<b>0071 34 4</b>	
	4	<b>0071 34 4</b>	10

## Assortments



Bolts and nuts  
UNF/SAE 8.8 /  $\gamma$  galv.,  
blue passivated  
Contents: 273 bolts from 1/4" x 1/2"  
to 5/16" x 2"  
and 220 nuts from 1/4" to 3/8"  
**Art. No. 0964 071**

Bolts and nuts  
UNC/USS 8.8 /  $\gamma$  galv.,  
blue passivated  
Contents: 273 bolts from 1/4" x 1/2"  
to 5/16" x 2"  
and 220 nuts from 1/4" to 3/8"  
**Art. No. 0964 072**

## Hexagon nuts UNF / SAE

Thread dia. (inches)	1"	1/2"	1/4"	3/4"	3/8"	5/16"	5/8"	7/16"	9/16"
Size in mm	37.30	19.05	11.11	28.18	14.29	12.70	23.81	17.46	22.22
Size in inches	1 15/32	3/4	7/16	1 7/64	9/16	1/2	15/16	11/16	7/8
No. of threads/inch	12	20	28	16	24	24	18	20	18

Dim. in inches	Steel 8 galv., blue passivated <b>Art. No.</b>	P. Qty.
1	<b>0331 1</b>	25
1/2	<b>0331 12</b>	
1/4	<b>0331 14</b>	
3/4	<b>0331 34</b>	25/100
3/8	<b>0331 38</b>	25

Dim. in inches	Steel 8 galv., blue passivated <b>Art. No.</b>	P. Qty.
5/16	<b>0331 516</b>	25
5/8	<b>0331 58</b>	
7/16	<b>0331 716</b>	
9/16	<b>0331 916</b>	