

1/2 INCH SOCKET WRENCH ASSORTMENT, DUST-PROTECTED



Dust-protected ratchet for a long service life even under difficult working conditions. With lever reverse.

High-quality, extensive 1/2 inch assortment including the most important wrench sizes

- Contents: 24 pieces
- Hex socket wrench inserts
- Hard foam with clamping effect, art. no. 095501224
- Metal box 405 x 165 x 50 mm, size 3, art. no. 09557153



reddot award 2015
winner

Art. No.	0965 012 240
P. Qty.	1
Number of pieces in assortment/set	24 PCS



Dust-proof ratchet head

- 1. Double sealing for better protection against dirt
- 2. Square drive: rugged and hard-wearing.

Maintenance-free – permanent lubrication of the mechanism is guaranteed.

Contents for Art. No.	Designation	Art. No.	Number
0965 012 240	1/2 inch lever reversible ratchet, dust-protected	0712 012 03	1
	1/2 inch socket wrench insert 10 mm	0712 131 110	1
	1/2 inch socket wrench insert 11 mm	0712 131 111	1
	1/2 inch socket wrench insert 12 mm	0712 131 112	1
	1/2 inch socket wrench insert 13 mm	0712 131 113	1
	1/2 inch socket wrench insert 14 mm	0712 131 114	1
	1/2 inch socket wrench insert 15 mm	0712 131 115	1
	1/2 inch socket wrench insert 16 mm	0712 131 116	1
	1/2 inch socket wrench insert 17 mm	0712 131 117	1
	1/2 inch socket wrench insert 18 mm	0712 131 118	1
	1/2 inch socket wrench insert 19 mm	0712 131 119	1
	1/2 inch socket wrench insert 20 mm	0712 131 120	1
	1/2 inch socket wrench insert 21 mm	0712 131 121	1
	1/2 inch socket wrench insert 22 mm	0712 131 122	1
	1/2 inch socket wrench insert 24 mm	0712 131 124	1
	1/2 inch socket wrench insert 26 mm	0712 131 126	1
	1/2 inch socket wrench insert 27 mm	0712 131 127	1
	1/2 inch socket wrench insert 28 mm	0712 131 128	1
	1/2 inch socket wrench insert 30 mm	0712 131 130	1
	1/2 inch socket wrench insert 32 mm	0712 131 132	1
1/2 inch angled extension 50 mm	0712 138 100	1	
1/2 inch extension 125 mm	0712 138 105	1	
1/2 inch extension 250 mm	0712 138 110	1	
1/2 inch cardan joint	0712 138 301	1	