

# SPIRALBOHRER – LIEFERÜBERSICHT

(d = Durchmesser, l1 = Gesamtlänge, l2 = Spannurlänge)

## Verpackungseinheiten:

| Art.-Nr. | 10 Stk.    | 5 Stk.    | 1 Stk.     |
|----------|------------|-----------|------------|
| 0624     | bis 8,0 mm | ab 8,1 mm | ab 10,5 mm |
| 0625     | bis 8,0 mm | ab 8,1 mm | ab 10,5 mm |
| 0626     | bis 4,5 mm | -         | ab 5 mm    |

| Abmessungen |       |       | Art.-Nr.    |          |          |
|-------------|-------|-------|-------------|----------|----------|
| d mm        | l1 mm | l2 mm | 0624 00 ... | 0625 ... | 0626 ... |
| 0,50        | 22    | 6     | 0 050       |          |          |
| 0,60        | 24    | 7     | 0 060       |          |          |
| 0,70        | 28    | 9     | 0 070       |          |          |
| 0,80        | 30    | 10    | 0 080       |          |          |
| 0,90        | 32    | 11    | 0 090       |          |          |
| 1,00        | 34    | 12    | 0 100       | 10       | 10       |
| 1,10        | 36    | 14    | 0 110       | 11       |          |
| 1,20        | 38    | 16    | 0 120       | 12       |          |
| 1,30        |       |       | 0 130       | 13       |          |
| 1,40        | 40    | 18    | 0 140       | 14       |          |
| 1,50        |       |       | 0 150       | 15       | 15       |
| 1,60        | 43    | 20    | 0 160       |          |          |
| 1,70        |       |       | 0 170       |          |          |
| 1,80        | 46    | 22    | 0 180       | 18       |          |
| 1,90        |       |       | 0 190       |          |          |
| 2,00        | 49    | 24    | 0 200       | 20       | 20       |
| 2,05        |       |       | 0 205       |          |          |
| 2,10        | 53    | 27    | 0 210       | 21       |          |
| 2,20        |       |       | 0 220       | 22       |          |
| 2,30        | 57    | 30    | 0 230       | 23       |          |
| 2,40        |       |       | 0 240       | 24       |          |
| 2,50        | 61    | 33    | 0 250       | 25       | 25       |
| 2,60        |       |       | 0 260       | 26       | 26       |
| 2,70        | 65    | 36    | 0 270       | 27       | 27       |
| 2,80        |       |       | 0 280       | 28       |          |
| 2,90        | 70    | 39    | 0 290       | 29       |          |
| 3,00        |       |       | 0 300       | 30       | 30       |
| 3,10        | 75    | 43    | 0 310       | 31       | 31       |
| 3,20        |       |       | 0 320       | 32       | 32       |
| 3,30        | 80    | 47    | 0 330       | 33       | 33       |
| 3,40        |       |       | 0 340       | 34       | 34       |
| 3,50        | 86    | 52    | 0 350       | 35       | 35       |
| 3,60        |       |       | 0 360       | 36       | 36       |
| 3,70        | 93    | 57    | 0 370       | 37       |          |
| 3,80        |       |       | 0 380       | 38       | 38       |
| 3,90        | 101   | 63    | 0 390       | 39       |          |
| 4,00        |       |       | 0 400       | 40       | 40       |
| 4,10        | 109   | 69    | 0 410       | 41       | 41       |
| 4,20        |       |       | 0 420       | 42       | 42       |
| 4,30        | 117   | 75    | 0 430       | 43       |          |
| 4,40        |       |       | 0 440       | 44       |          |
| 4,50        | 125   | 81    | 0 450       | 45       | 45       |
| 4,60        |       |       | 0 460       | 46       |          |
| 4,70        | 133   | 87    | 0 470       | 47       |          |
| 4,80        |       |       | 0 480       | 48       |          |
| 4,90        | 142   | 94    | 0 490       | 49       |          |
| 5,00        |       |       | 0 500       | 50       | 50       |
| 5,10        | 151   | 101   | 0 510       | 51       |          |
| 5,20        |       |       | 0 520       | 52       | 52       |
| 5,30        | 160   | 108   | 0 530       | 53       |          |
| 5,40        |       |       | 0 540       | 54       |          |
| 5,50        | 169   | 114   | 0 550       | 55       | 55       |
| 5,60        |       |       | 0 560       | 56       |          |
| 5,70        | 178   | 120   | 0 570       | 57       |          |
| 5,80        |       |       | 0 580       | 58       |          |
| 5,90        | 184   | 125   | 0 590       |          |          |
| 6,00        |       |       | 0 600       | 60       | 60       |
| 6,10        | 191   | 130   | 0 610       | 61       |          |
| 6,20        |       |       | 0 620       | 62       |          |
| 6,30        | 198   | 135   | 0 630       | 63       |          |
| 6,40        |       |       | 0 640       | 64       |          |
| 6,50        | 205   | 140   | 0 650       | 65       | 65       |
| 6,60        |       |       | 0 660       | 66       |          |
| 6,70        |       |       | 0 670       | 67       |          |

| Abmessungen |       |       | Art.-Nr.    |          |          |     |     |
|-------------|-------|-------|-------------|----------|----------|-----|-----|
| d* mm       | l1 mm | l2 mm | 0624 00 ... | 0625 ... | 0626 ... |     |     |
| 6,80        | 109   | 69    | 0 680       | 68       |          |     |     |
| 6,90        |       |       | 0 690       | 69       |          |     |     |
| 7,00        |       |       | 0 700       | 70       | 70       |     |     |
| 7,10        |       |       | 0 710       | 71       |          |     |     |
| 7,20        |       |       | 0 720       | 72       |          |     |     |
| 7,30        |       |       | 0 730       | 73       |          |     |     |
| 7,40        |       |       | 0 740       | 74       |          |     |     |
| 7,50        |       |       | 0 750       | 75       | 75       |     |     |
| 7,60        |       |       | 117         | 75       | 0 760    | 76  |     |
| 7,70        |       |       |             |          | 0 770    | 77  |     |
| 7,80        | 0 780 | 78    |             |          |          |     |     |
| 7,90        | 0 790 | 79    |             |          |          |     |     |
| 8,00        | 0 800 | 80    |             |          | 80       |     |     |
| 8,10        | 0 810 | 81    |             |          |          |     |     |
| 8,20        | 0 820 | 82    |             |          |          |     |     |
| 8,30        | 0 830 | 83    |             |          |          |     |     |
| 8,40        | 0 840 | 84    |             |          |          |     |     |
| 8,50        | 0 850 | 85    |             |          | 85       |     |     |
| 8,60        | 125   | 81    | 0 860       | 86       |          |     |     |
| 8,70        |       |       | 0 870       | 87       |          |     |     |
| 8,80        |       |       | 0 880       | 88       |          |     |     |
| 8,90        |       |       | 0 890       | 89       |          |     |     |
| 9,00        |       |       | 0 900       | 90       | 90       |     |     |
| 9,10        |       |       | 0 910       | 91       |          |     |     |
| 9,20        |       |       | 0 920       | 92       |          |     |     |
| 9,30        |       |       | 0 930       |          |          |     |     |
| 9,40        |       |       | 0 940       | 94       |          |     |     |
| 9,50        |       |       | 0 950       | 95       | 95       |     |     |
| 9,60        | 133   | 87    | 0 960       | 96       |          |     |     |
| 9,70        |       |       | 0 970       | 97       |          |     |     |
| 9,80        |       |       | 0 980       | 98       |          |     |     |
| 9,90        |       |       | 0 990       | 99       |          |     |     |
| 10,00       |       |       | 1 000       | 100      | 100      |     |     |
| 10,10       |       |       | 1 010       | 101      |          |     |     |
| 10,20       |       |       | 1 020       | 102      | 102      |     |     |
| 10,30       |       |       | 1 030       |          |          |     |     |
| 10,50       |       |       | 1 050       | 105      | 105      |     |     |
| 10,60       |       |       | 1 060       |          |          |     |     |
| 10,80       | 1 080 |       |             |          |          |     |     |
| 11,00       | 142   | 94    | 1 100       | 110      | 110      |     |     |
| 11,10       |       |       | 1 110       |          |          |     |     |
| 11,20       |       |       | 1 120       |          |          |     |     |
| 11,50       |       |       | 1 150       | 115      | 115      |     |     |
| 12,00       | 151   | 101   | 1 200       | 120      | 120      |     |     |
| 12,10       |       |       | 1 210       |          |          |     |     |
| 12,20       |       |       | 1 220       |          |          |     |     |
| 12,30       |       |       | 1 230       |          |          |     |     |
| 12,50       |       |       | 1 250       | 125      | 125      |     |     |
| 13,00       |       |       | 1 300       | 130      | 130      |     |     |
| 13,10       |       |       | 1 310       |          |          |     |     |
| 13,50       |       |       | 160         | 108      | 1 350    | 135 |     |
| 14,00       |       |       |             |          | 1 400    | 140 | 140 |
| 14,20       |       |       | 169         | 114      | 1 420    |     |     |
| 14,50       | 1 450 | 145   |             |          |          |     |     |
| 15,00       | 1 500 | 150   |             |          | 150      |     |     |
| 15,50       | 178   | 120   | 1 550       | 155      |          |     |     |
| 16,00       |       |       | 1 600       | 160      | 160      |     |     |
| 16,50       | 184   | 125   | 1 650       | 165      |          |     |     |
| 17,00       |       |       | 1 700       | 170      |          |     |     |
| 17,50       |       |       | 1 750       | 175      |          |     |     |
| 18,00       | 191   | 130   | 1 800       | 180      |          |     |     |
| 18,50       |       |       | 1 850       | 185      |          |     |     |
| 19,00       | 191   | 130   | 1 900       | 190      |          |     |     |
| 19,50       |       |       | 1 950       | 195      |          |     |     |
| 20,00       | 2 000 | 200   |             |          |          |     |     |