

Araç tipi	Ön cam	Şek.	Ayar ölç. (mm)	Arka cam	Şek.	Ayar ölç. (mm)	Ön ve arka cam	Şek.	Ayar ölç. (mm)	Yan cam	Şek.	Ayar ölç. (mm)
Mercedes-Benz E-Sınıfı (W 210)	0696 576	4					0696 579	4				
Mercedes-Benz S-Sınıfı (W 140)	0696 514 3	3.1	22,0				0696 511 4	4				
Mercedes-Benz S-Sınıfı (W 220) (10.98♦)	0696 517 1	2					0696 576	4				
Mercedes-Benz 200-300 E (W124)	0696 587	4		0696 576	4					0696 579	4	
	0696 514 3	3.1	18,5	0696 573	1							
Mercedes-Benz Roadster (R129)							0696 579	4		0696 579	4	
Mercedes-Benz Sprinter	0696 520 9	8										
	0696 579	4										
Mercedes-Benz Vaneo (2001♦)	0696 520 7	8										
	0696 579	4										
Mercedes M-Sınıfı	0696 520 8	8										
	0696 520 9	8										
	0696 579	4										
Mitsubishi, 1985'den itibaren tüm modeller	0696 520 8	8		0696 579	4		0696 511 8	4				
	0696 520 7	8										
	0696 579	4										
Nissan Bluebird U II/Caravan	0696 511 8	4										
Nissan Cherry/Pulsar	0696 511 8	4										
Nissan Cedric	0696 511 8	4										
	0696 579	4										
Nissan Fair Lady/Low Laurel	0696 511 8	4										
Nissan Pulsar Modell 87/Skyline (R 30)							0696 511 8	4				
Nissan Skyline Excel (R 31)				0696 511 8	4							
Nissan Stanza	0696 597	2										
Nissan Terrano II	0696 576	4		0696 514 3	3.1	18,0				0696 514 3	3.1	20,0
				0696 515 7	4					0696 516 0	2	
Nissan (tümü)	0696 520 8	8										
	0696 520 7	8										
	0696 579	4										
Opel Agila	0696 520 7	8										
	0696 579	4										
Opel Ascona				0696 514 3	3.1	18,5						
Opel Astra				0696 579	4		0696 576	4				
Opel Astra "Caravan" (98♦)							0696 516 3	4				
Opel Astra "Hatch back (98♦)"	0696 516 3	4		0696 519 4	2							
				0696 514 3	3.1	20,0						
				0696 516 9	3.1	76,0/71,0						
Opel Calibra	0696 576	4		0696 512 2	2							
	0696 510 7	4		0696 512 3	2							
Opel Corsa B	0696 579	4					0696 576	4				
Opel Corsa C (2001♦)	0696 520 7	8										
	0696 579	4										
Opel Frontera	0696 579	4								0696 579	4	
										0696 512 5	2	
										0696 514 3	3.1	27,0/23,0
Opel Kadett E "Form back"	0696 510 1	4				0696 576	4		0696 510 3	5		
Opel Kadett E "Hatch back"	0696 576	4		0696 514 3	3.1	30,5				0696 510 3	5	
	0696 510 1	4										
Opel Kadett E "Caravan"	0696 576	4		0696 514 3	3.1	19,0				0696 510 3	5	
	0696 510 1	4										
Opel Movano	0696 520 9	8										
	0696 579	4										
Opel Omega A	0696 510 7	4		0696 510 9	5							
	0696 510 8	4										
Opel Omega B (Mod. 94♦)	0696 576	4										
	0696 510 7	4										
Opel Omega B "Caravan" (Mod. 94♦)	0696 510 7	4					0696 576	4				
Opel Senator	0696 510 7	4		0696 510 9	5							
	0696 510 8	4										
	0696 512 0	5										
Opel Tigra	0696 510 7	4		0696 512 3	2							
	0696 576	4		0696 517 2	5							
				0696 517 3	2							
Opel Vectra "Form back"						0696 576	4					
Opel Vectra "Hatch back"	0696 576	4		0696 512 1	1							
				0696 512 2	2							
				0696 512 3	2							
Opel Vectra B (95♦) Hatch back	0696 579	4		0696 519 4	2							
				0696 512 3	2							