



# Skrutky do plechu so zápusťnou hlavou

s krížovou drážkou H,  
tvar C, s hrotom

podľa: **DIN 7982**

**ISO 7050**

**STN 02 1237**

- Oceľ pozinkovaná namodro
- Oceľ pozinkovaná zažlto
- Ušľachtilá oceľ A2

Menovitý Ø d mm	2,2	2,9	3,5	3,9	4,2	4,8	5,5	6,3
dk mm	4,3	5,5	6,8	7,5	8,1	9,5	10,8	12,4
k mm	1,3	1,7	2,1	2,3	2,5	3,0	3,4	3,8
Drážka	H1	H1	H2	H2	H2	H2	H3	H3

Menovitý Ø d mm	Dĺžka l mm	Oceľ pozink. namodro Obj.č.	Bal./ks	Oceľ pozink. nažlto Obj.č.	Bal./ks	A2 Obj.č.	Bal./ks
2,2	6,5	116 22 65	100/1000				
	9,5	116 22 95	500				
2,9	6,5	116 29 65	100/1000	116 029 65	2000	123 29 65	1000
	9,5	116 29 95				123 29 95	300/1000
	13	116 29 13	123 29 13				
	16	116 29 16	123 29 16				
	19	116 29 19	123 29 19				
	22	116 29 22	100/1000			123 29 22	300
	25	116 29 25				123 29 25	
	45	116 29 45	100				
3,5	9,5	116 35 95	300/1000	116 035 95	1000	123 35 95	300/1000
	13	116 35 13				123 35 13	
	16	116 35 16				123 35 16	
	19	116 35 19				123 35 19	
	22	116 35 22	300			123 35 22	
	25	116 35 25	100/1000			123 35 25	100/1000
	32	116 35 32				123 35 32	
	38	116 35 38				123 35 38	
	45					123 35 45	1000
	50					123 35 50	100/1000
60			123 35 60	1000			
3,9	9,5	116 39 95	300/1000	116 039 13	1000	123 39 95	300/1000
	13	116 39 13				123 39 13	
	16	116 39 16				123 39 16	
	19	116 39 19	100/1000	116 039 19		123 39 19	
	22	116 39 22	300/1000	116 039 22		123 39 22	
	25	116 39 25	100/1000	116 039 25		123 39 25	
	32	116 39 32		116 039 32		123 39 32	
	38	116 39 38		116 039 38		123 39 38	
	45	116 39 45				123 39 45	250/1000
	50	116 39 50				123 39 50	500
60				123 39 60			
4,2	9,5	116 42 95	100/1000			123 42 95	300/1000
	13	116 42 13	300/1000			123 42 13	
	16	116 42 16		123 42 16			
	19	116 42 19		123 42 19			
	22	116 42 22	100/1000			123 42 22	
	25	116 42 25		123 42 25			
	32	116 42 32		123 42 32			
	38	116 42 38		123 42 38			
	45	116 42 45		123 42 45			
	50	116 42 50		123 42 50			
	60	116 42 60	100			123 42 60	500
70	116 42 70	100/500			123 42 70		

## Sada skrutiek



**Pozinkované skrutky,  
podľa DIN 7982 / STN 02 1237**

Obsah: 16 veľkostí od 3,5×13 do 4,8×50, spolu 1500 kusov.

Kovový kufrík s plastovou vložkou so 16 priehradkami.

**Obj.č. 964 116**