

Araç tipi	Ön cam	Şek.	Ayar ölç. (mm)	Arka cam	Şek.	Ayar ölç. (mm)	Ön ve arka cam	Şek.	Ayar ölç. (mm)	Yan cam	Şek.	Ayar ölç. (mm)
Opel Vectra B (95♦) Formheck	0696 579	4		0696 576	4							
Opel Vivaro	0696 520 7	8										
	0696 579	4										
Opel Zafira	0696 520 7	8		0696 520 8	8							
	0696 579	4										
Peugeot 106	0696 576	4		0696 514 3	3.1	17,0						
	0696 514 3	3.1	16,0	0696 514 4	6							
	0696 514 6	6										
Peugeot 205				0696 582	3.2							
				0696 583	4							
Peugeot 206	0696 579	4		0696 514 3	3.1							
				0696 512 5	2							
Peugeot 306	0696 579	4		0696 514 3	3.1	28,0						
	0696 514 3	3.1	16,0	0696 516 0	2							
	0696 514 6	6		0696 514 4	6							
Peugeot 405							0696 576	4				
Peugeot 406				0696 514 3	3.1					0696 514 3	3.1	Arka
				0696 515 4	4							
Peugeot 406 Coupé				0696 519 4	2		0696 514 3	3.1				
							0696 515 4	4				
Peugeot 605	0696 515 4	4					0696 576	4				
Peugeot 806	0696 576	4		0696 514 3	3.1	29,5				0696 510 3	5	
	0696 579	4		0696 581	2					0696 512 5	2	
Peugeot Boxer	0696 520 9	8										
	0696 579	4										
Porsche 911, Carrera 4							0696 510 3	5		0696 510 3	5	
Porsche 911, Carrera (993)	0696 512 2	2		0696 511 8	4		0696 516 4	5		0696 510 3	5	
Porsche 924/944 (2.85♦)	0696 572	3.2										
	0696 511 4	4										
Porsche 928 S4	0696 512 7	4										
Porsche, Boxter	0696 520 7	8										
	0696 515 4	4										
Renault Super 5	0696 576	4										
	0696 514 3	3.1	18,5									
	0696 510 3	5										
	0696 573	1										
Renault 19	0696 576	4		0696 579	4							
Renault 21	0696 511 5	4		0696 576	4							
	0696 510 7	4										
	0696 511 1	4										
Renault 25	0696 579	4		0696 514 3	3.1	27,0						
	0696 576	4										
	0696 573	1										
Renault Clio	0696 579	4										
Renault Espace	0696 573	1								0696 573	1	Ön
	0696 514 3	3.1	25,0							0696 595	4	Ön
	0696 576	4								0696 573	1	Arka
										0696 576	4	Arka
Renault Espace (Modell 91)	0696 520 7	8								0696 597	2	Açılabilir Yan cam
										0696 510 4	5	Açılabilir- Yan cam
										0696 576	4	Sabit Yan cam
Renault Laguna	0696 576	4		0696 514 3	3.1	30,0				0696 514 3	3.1	
	0696 581	2		0696 581	2					0696 512 5	2	
										0696 631		Sägebl.
Renault Medaillon	0696 576	4										
	0696 511 1	4										
Renault Megane (3-kapılı)							0696 576	4		0696 573	1	
Renault Megane (5-kapılı)	0696 576	4								0696 514 3	3.1	25,0/27,0
Renault Safrane	0696 510 7	4		0696 514 3	3.1	30,0				0696 510 4	5	
	0696 511 5	4		0696 516 0	2							
				0696 512 5	2							
Renault Twingo	0696 579	4										
Renault FR 1 u. PR 4 (Bus)										0696 511 0	4	
Renault PR 14 (Bus)	0696 576	4								0696 576	4	
Renault R 312 (Bus)										0696 511 0	4	
										0696 510 8	4	
Renault SC 10 (Bus)	0696 514 3	3.1	35,0									
	0696 573	1										
Renault AE (LKW)	0696 520 9	8								0696 576	4	
Renault R 310 (LKW)	0696 514 3	3.1	35,0									
	0696 511 0	4										
Rover 214	0696 514 3	3.1	24,0	0696 519 5	3.1	42,0						
	0696 511 0	4										