



Tornavida TX

Şaft: Yuvarlak uç, mat kromajlı.
Kafa tipi: İç TX, Black Point.

A	B/C		A	Art.-Nr.	
	A mm	B/C mm			
TX 06	60	73/20	2 3/8"	0613 434 06	1
TX 07	60	73/20	2 3/8"	0613 434 07	
TX 08	60	83/27	2 3/8"	0613 434 08	
TX 09	60	83/27	2 3/8"	0613 434 09	
TX 10	80	83/27	3 1/8"	0613 434 10	
TX 15	80	96/31	3 1/8"	0613 434 15	
TX 20	100	96/31	4"	0613 434 20	
TX 25	100	106/35	4"	0613 434 25	
TX 27	115	106/35	4 9/16"	0613 434 27	
TX 30	115	106/35	4 9/16"	0613 434 30	
TX 40	130	114/38	5 3/16"	0613 434 40	
TX 45	130	114/38	5 3/16"	0613 434 45	



Tornavida Takımı

TX tornavida

Art.-Nr. 0613 934 8

A	Art.-Nr.	A	Art.-Nr.	
A mm	Art.-Nr.	A mm	Art.-Nr.	
TX 10	0613 434 10	TX 27	0613 434 27	1
TX 15	0613 434 15	TX 30	0613 434 30	
TX 20	0613 434 20	TX 40	0613 434 40	
TX 25	0613 434 25	TX 45	0613 434 45	



Tornavida TX

Şaft: Yuvarlak uç, uzun model, mat kromajlı.

Kafa tipi: İç TX, Black Point.

Kullanım:

- TX 10 VW Gösterge paneli
- TX 15 BMW Kapı kulbu
- TX 20 Daimler-Chrysler, A- ve C-sınıfı
- TX 25 VW Sharan, Farlar
- TX 30 BMW 7 Serisi (E 38) çamurluk civataları, Audi A4/A6 Farlar



A	B/C		A	Art.-Nr.	
	A mm	B/C mm			
TX 10	250	83/27	10"	0613 464 10	1
TX 15	250	96/31	10"	0613 464 15	
TX 20	250	96/31	10"	0613 464 20	
TX 25	250	106/35	10"	0613 464 25	
TX 30	250	106/35	10"	0613 464 30	

Tornavida Takımı

TX tornavida, uzun model

Art.-Nr. 0613 964 5

A	Art.-Nr.	A	Art.-Nr.	
A mm	Art.-Nr.	A mm	Art.-Nr.	
TX 10	0613 464 10	TX 25	0613 464 25	1
TX 15	0613 464 15	TX 30	0613 464 30	
TX 20	0613 464 20			