

## Premium rim cleaner

**Acid-free special cleaner for all steel and light-alloy wheel rims**

**Colour change indicates that product is working**

**Easy-to-clean finish**

Reduced adhesion of brake dust by the formation of a protective film on the wheel rim.

**Acid-free, powerful additive concentration**

- Protects rim surface and wheel bolts
- Even removes flash rust particles
- Simple and sparing to use

**Aerosol can with pure air as propellant**

- 360° application: Sprays in all positions
- Perfect spray finish

**No flammable or harmful propellant gases**

**Product is not mixed with propellant**

- Almost complete emptying
- Optimum protection of product

**Safe**

- Does not make any explosive vapour/air mixtures
- When applied correctly, does not impair/damage coalescence separators




Chemical basis	Mixture of surfactants and selected complex compounds
Smell/fragrance	Characteristic
Colour	Yellow green
pH value/conditions	7.5/undiluted
Density/conditions	1.08 g/cm <sup>3</sup> /at 20°C
Shelf life from production	24 Month
AOX-free	Yes
Silicone-free	Yes
Bio-degradable	Yes
Free of phosphoric acid	Yes

Contents	Container	Art. no.	P. Qty.
400 ml	Aerosol can	<b>0893 476 500</b>	1/6
5 l	Canister	<b>0893 476 505</b>	1
20 l	Canister	<b>0893 476 520</b>	1

## Details/Application

The acid-free combination of active agents removes even the most stubborn dirt, such as firmly adhering brake abrasion, road dirt, oil and rubber residues and surface rust particles from all steel and light-alloy rims.



## Instructions

Spray the wheel rims completely and evenly from a short distance (approx. 20 cm). Allow to soak in for 3–5 minutes depending on the degree of soiling. The active agent turns from red to violet while taking effect. Then thoroughly rinse off with a strong water jet or a high-pressure cleaner. Particularly with stubborn dirt, rough surfaces or in corners, the cleaning effect can be increased by using the Würth hand and wheel rim brush.

## Notice

Do not apply to hot wheel rims or in direct sunlight, and do not allow to dry. Protect from frost.  
For more information, please refer to the technical data sheet.

The usage instructions are recommendations based on the tests we have conducted and our experience; carry out your own tests before each application. Due to the large number of applications and storage and processing conditions, we do not assume any liability for a specific application result. Insofar as our free customer service provides technical information or acts as an advisory service, no responsibility is assumed by this service except where the advice or information given falls within the scope of our specified, contractually agreed service or the advisor was acting deliberately. We guarantee consistent quality of our products. We reserve the right to make technical changes and further develop products.

### Related products

Hand brush  
Rim brush

### Art. no.

**0891 350 102**  
**0891 350 211**

<b>Related products for</b>	<b>Designation</b>	<b>Art. no.</b>
0893 476 505	Product-specific pump spray bottle Unfilled	<b>0891 503 004</b>
	Pump spray bottle Perfect Foam	<b>0891 503 021</b>
0893 476 520	Pump spray bottle Perfect Foam	<b>0891 503 021</b>