

ZYLINDERSCHRAUBEN

mit Schlitz
nach DIN 84 (ISO 1207)

| Nenn-Ø d | Länge l mm | Messing blank Art.-Nr. | VE/St. | Stahl 4.8 blank Art.-Nr. | VE/St. | Stahl 4.8 vz., blau pass. Art.-Nr. | VE/St. | Stahl 4.8 vz., gelb pass. Art.-Nr. | VE/St. | A2  Art.-Nr. | VE/St. | A4  Art.-Nr. | VE/St. |
|----------|------------|------------------------|-------------|--------------------------|--------------|------------------------------------|--------------|------------------------------------|-------------|---|---------|---|--------|
| M 2,5 | 25 | | | 0040 025 25 | 2000 | 0040 25 25 | 100/500 | 0040 725 25 | 500 | | | | |
| | 28 | | | 0040 025 28 | | 0040 25 28 | 2000 | | | | | | |
| | 30 | | | 0040 025 30 | | 0040 25 30 | | | 0040 725 30 | 2000 | | | |
| | 40 | | | | | 0040 25 40 | 100 | | | | | | |
| M 3 | 3 | | | 0040 03 3 | 2000 | 0040 3 3 | 2000 | 0040 73 3 | 2000 | 0287 3 3 | 1000 | | 1000 |
| | 4 | 0001 3 4 | 2000 | 0040 03 4 | | 0040 3 4 | 100/500 | 0040 73 4 | | 0287 3 4 | | | |
| | 5 | 0001 3 5 | 100/500 | 0040 03 5 | | 0040 3 5 | | 0040 73 5 | | 0287 3 5 | | | |
| | 6 | 0001 3 6 | | 0040 03 6 | | 0040 3 6 | 100/1000 | 0040 73 6 | | 0287 3 6 | | | |
| | 8 | 0001 3 8 | 250 | 0040 03 8 | | 0040 3 8 | 500/1000 | 0040 73 8 | | 0287 3 8 | | | |
| | 10 | 0001 3 10 | | 0040 03 10 | | 0040 3 10 | | 500/1000 | | 0040 73 10 | | 0287 3 10 | |
| | 12 | 0001 3 12 | | 0040 03 12 | | 0040 3 12 | | 0040 73 12 | | 0287 3 12 | | | |
| | 14 | 0001 3 14 | 2000 | 0040 03 14 | | 0040 3 14 | 2000 | 0040 73 14 | | 0287 3 14 | | | |
| | 16 | 0001 3 16 | 250 | 0040 03 16 | | 0040 3 16 | 100/500 | 0040 73 16 | | 0287 3 16 | | | |
| | 18 | 0001 3 18 | 2000 | 0040 03 18 | | 0040 3 18 | | 100/500 | | 0040 73 18 | | 0287 3 18 | |
| | 20 | 0001 3 20 | 250 | 0040 03 20 | | 0040 3 20 | 2000 | 0040 73 20 | | 0287 3 20 | | | |
| | 22 | 0040 03 22 | | 0040 3 22 | | 0040 73 22 | | 0287 3 22 | | | | | |
| | 25 | 0001 3 25 | | 0040 03 25 | | 0040 3 25 | | 100/250/1000 | | 0040 73 25 | | 0287 3 25 | |
| | 28 | | | 0040 03 28 | | 0040 3 28 | | 2000 | | 0040 73 28 | | | |
| | 30 | 0001 3 30 | | 0040 03 30 | | 0040 3 30 | 100/500 | 0040 73 30 | | 0287 3 30 | | | |
| | 32 | | | 0040 03 32 | | 0040 3 32 | 1000 | | | | | | |
| | 35 | 0001 3 35 | | 0040 03 35 | | 0040 3 35 | 100/250/1000 | 0040 73 35 | | 0287 3 35 | | | |
| | 38 | | 1000 | 0040 03 38 | | 0040 3 38 | 2000 | | | | | | |
| | 40 | 0001 3 40 | | 0040 03 40 | | 0040 3 40 | 100/250/1000 | 0040 73 40 | | 0287 3 40 | | | |
| | 45 | 0001 3 45 | | 0040 03 45 | | 0040 3 45 | 100/300 | 0040 73 45 | | 0287 3 45 | | | |
| 50 | 0001 3 50 | 250 | 0040 03 50 | 0040 3 50 | 100/250 | 0040 73 50 | 0287 3 50 | | | | | | |
| 55 | | | 0040 03 55 | 0040 3 55 | 500 | 0040 73 55 | 0287 3 55 | | | | | | |
| 60 | | | 0040 03 60 | 0040 3 60 | 100/250 | 0040 73 60 | 0287 3 60 | | | | | | |
| M 3,5 | 5 | | | 0040 035 5 | 2000 | 0040 35 5 | 2000 | 0040 735 5 | 2000 | | 500 | | |
| | 6 | | | 0040 035 6 | | 0040 35 6 | | 0040 735 6 | | | | | |
| | 8 | | | 0040 035 8 | | 0040 35 8 | | 0040 735 8 | | | | | |
| | 10 | | | 0040 035 10 | | 0040 35 10 | | 0040 735 10 | | | | | |
| | 12 | | | 0040 035 12 | | 0040 35 12 | | 0040 735 12 | | | | | |
| | 14 | | | 0040 035 14 | | 0040 35 14 | | | | | | | |
| | 16 | | | 0040 035 16 | | 0040 35 16 | | 0040 735 16 | | | | | |
| | 18 | | | 0040 035 18 | | 0040 35 18 | | | | | | | |
| | 20 | | | 0040 035 20 | | 0040 35 20 | | 0040 735 20 | | | | | |
| | 22 | | | 0040 035 22 | | 0040 35 22 | | 0040 735 22 | | | | | |
| | 25 | | | 0040 035 25 | | 0040 35 25 | | 0040 735 25 | | | | | |
| | 28 | | | 0040 035 28 | | 0040 35 28 | | | | | | | |
| | 30 | | | 0040 035 30 | | 0040 35 30 | | 0040 735 30 | | | | | |
| | 32 | | | 0040 035 32 | | 0040 35 32 | | | | | | | |
| | 35 | | | 0040 035 35 | | 0040 35 35 | | | | | | | |
| | 38 | | | 0040 035 38 | | 0040 35 38 | | | | | | | |
| 40 | | | 0040 035 40 | 0040 35 40 | | | | | | | | | |
| 45 | | | 0040 035 45 | 0040 35 45 | | | | | | | | | |
| 50 | | | 0040 035 50 | 0040 35 50 | | | | | | | | | |
| 55 | | | 0040 035 55 | 0040 35 55 | 500 | | | | | | | | |
| 60 | | | 0040 035 60 | 0040 35 60 | | | | | | | | | |
| M 4 | 4 | | | 0040 04 4 | 2000 | 0040 4 4 | 100/500 | 0040 74 4 | 2000 | | 200/500 | | 1000 |
| | 5 | 0001 4 5 | 500/2000 | 0040 04 5 | | 0040 4 5 | 100/500/1000 | 0040 74 5 | | 0287 4 5 | | | |
| | 6 | 0001 4 6 | 250 | 0040 04 6 | | 0040 4 6 | 100/500 | 0040 74 6 | | 0287 4 6 | | | |
| | 8 | 0001 4 8 | | 0040 04 8 | | 0040 4 8 | 100/250/1000 | 0040 74 8 | | 0287 4 8 | | | |
| | 10 | 0001 4 10 | | 0040 04 10 | | 0040 4 10 | 100/250/1000 | 0040 74 10 | | 0287 4 10 | | | |
| | 12 | 0001 4 12 | | 0040 04 12 | | 0040 4 12 | 100/250 | 0040 74 12 | | 0287 4 12 | | | |
| | 14 | 0001 4 14 | 2000 | 0040 04 14 | | 0040 4 14 | 100 | 0040 74 14 | | | | | |
| | 16 | 0001 4 16 | 250 | 0040 04 16 | | 0040 4 16 | 250/1000 | 0040 74 16 | | 0287 4 16 | | | |
| | 18 | 0001 4 18 | 200 | 0040 04 18 | | 0040 4 18 | 100/1000 | 0040 74 18 | | 0287 4 18 | | | |
| | 20 | 0001 4 20 | 250 | 0040 04 20 | | 0040 4 20 | 100/250/1000 | 0040 74 20 | | 0287 4 20 | | | |
| 22 | | | 0040 04 22 | 0040 4 22 | 2000 | 0040 74 22 | 0287 4 22 | | | | | | |
| 25 | 0001 4 25 | | 0040 04 25 | 0040 4 25 | 100/250/1000 | 0040 74 25 | 0287 4 25 | | | | | | |
| 28 | | 250 | 0040 04 28 | 0040 4 28 | 2000 | 0040 74 28 | | | | | | | |
| 30 | 0001 4 30 | | 0040 04 30 | 0040 4 30 | 100/250/1000 | 0040 74 30 | 0287 4 30 | | | | | | |