




ORSY



Flügelmuttern ähnlich DIN 315 Amerikanische Form


Stahl verzinkt,
blau passiviert

A2, A4 (ähnl. DIN)

Gew.-Ø d	d ₁ mm	e mm	h mm	g mm	Stahl vz., blau pass. Art.-Nr.	VE/St.	A2 ähnl. DIN 314 Art.-Nr.	VE/St.	A4 ähnl. DIN 314 Art.-Nr.	VE/St.	
M3	6	12,6	6,4	1,1	0342 3	100		25	0340 033	100	
M4	8	17,6	8,6	1,6	0342 4				0344 04		0340 034
M5	10,3	22,5	11	2,1	0342 5				0344 05		0340 035
M6	12,7	27,8	13,6	2,5	0342 6				0344 06		0340 036
M8	13,8	30,3	14,8	2,8	0342 8				0344 08		0340 038
M10	16,5	36,2	17,7	3,3	0342 10	50	0344 010	10	0340 031 0	50	
M12	22,5	49,4	24,1	4,5	0342 12	25	0344 012	5	0340 031 2		
M14	28,5	59,4	31,1	5,7	0342 14		0340 031 4				
M16	34,5	61	38,2	6,9	0342 16		0340 031 6	20			



ORSY




Flügelmuttern DIN 315

Temperguss
A2
A4

Gew.-Ø d	d ₁ mm	e mm	h mm	g mm	Temperguss Art.-Nr.	VE/St.	A2 Art.-Nr.	VE/St.	A4 Art.-Nr.	VE/St.
M4	6	18	8,5	1,9	0342 04	100	0344 004	100	0340 044	100
M5	8	24	11	2,3	0342 05		0344 005		0340 045	
M6	10	30	15	2,3	0342 06		0344 006	50	0340 046	50
M8	13	36	18	2,8	0342 08		0344 008		0340 048	
M10	17	48	23	4,4	0342 010	50	0344 001 0	20	0340 041 0	20
M12	20	62	31	4,9	0342 012	25	0344 001 2		0340 041 2	
M16	26	70	35	6,4	0342 016		0344 001 6		0340 041 6	
M20	32	86	44	6,9	0342 020	10		0340 042 0		



ORSY



Flügel- schrauben DIN 316

Temperguss

Gew.-Ø d	M4	M5	M6	M8	M10
d ₁ mm	6	8	10	13	17
e mm	18	24	30	36	48
h mm	8,5	11	15	18	23
g mm	1,9	2,3	2,3	2,8	4,4

Gew.-Ø d → l mm ↓	M4 Temperguss Art.-Nr.	VE/St.	M5 Temperguss Art.-Nr.	VE/St.	M6 Temperguss Art.-Nr.	VE/St.	M8 Temperguss Art.-Nr.	VE/St.	M10 Temperguss Art.-Nr.	VE/St.	M12 Temperguss	VE/St.
10			0237 5 10	250	0237 6 10	250	0237 8 10	50				
12			0237 5 12		0237 6 12		0237 8 12					
16	0237 4 16	250	0237 5 16		0237 6 16		0237 8 16		0237 10 16	50		
18							0237 8 18					
20	0237 4 20	250	0237 5 20	250	0237 6 20	50	0237 8 20	50	0237 10 20		0237 12 20	25
25			0237 5 25		0237 6 25		0237 8 25		0237 10 25		0237 12 25	
30	0237 4 30	250	0237 5 30	100	0237 6 30	50	0237 8 30	50	0237 10 30		0237 12 30	
35			0237 5 35		0237 6 35		0237 8 35		0237 10 35		0237 12 40	
40			0237 5 40		0237 6 40		0237 8 40		0237 10 40		0237 12 40	25
50					0237 6 50	50	0237 8 50		0237 10 50		0237 12 50	
60					0237 6 60	100			0237 10 60		0237 12 60	