

## PNEUMATIC IMPACT WRENCH



**Reliable, powerful impact wrench with fast torque build-up.**  
**Recommended maximum bolt size: M15. Ideal for changing tires.**

**DSS 1/2" H**  
**Art. No. 0703 736 0**  
 P. Qty. 1

**Rugged and well-balanced unit featuring an aluminum housing.** Long service life and optimum center of gravity.

**Rubber-coated and ergonomically-shaped handle, user-friendly clockwise/ counterclockwise switching and adjustable trigger.**

The handle does not become cool during work. The device is very handy and user-friendly.

**High-quality pin impact mechanism in oil tank with six-vane motor.**

Increased service life thanks to constant lubrication. Nearly vibration-free.

**3-year warranty.**  
 On manufacturing and material defects.

**Available in the fleet management system ORSY®fleet.**

Technical data		
Type		DSS 1/2" H
Square drive		1/2"
Working torque*	in Nm	70 - 470
Max. releasing torque	in Nm	569
Avg. operating pressure	in bar	6.3
Weight	in kg	2.3
Dimensions	(L x W x H) in mm	195 x 64 x 202
Avg. air consumption in	L/min	102
Connection thread	in inches	1/4"
Minimum hose dia.	in mm	8
Sound pressure level	in db(A)	92

\* The working torque is the torque usually achieved under average working conditions. It depends on the highly varying ambient conditions (air pressure, hose diameter, soiling etc.).

Accessories		
Designation	Art. No.	P. Qty.
Plug-In Nipple with R 1/4" male thread made of nickel-plated steel	<b>0699 100 614</b>	3
Small Mist Oiler with 1/4" female thread	<b>0699 070 314</b>	1
Special Oil for pneumatic tools (1 L)	<b>0893 050 5</b>	
1/2" Power Socket Wrench Sets	<b>0714 13 ...</b>	

When used regularly, the machine should be lightly oiled via the compressed-air supply every day. The use of a mist oiler is recommended.



The reversing piston and the four tightening torque stages can be operated with one hand and enable optimum adaptation to the task at hand.