



## FILLISTER-HEAD SCREWS



Can be stored in ORSY® system

Nominal dia. d	M 2	M 2.5	M 3	M 3.5	M 4	M 5	M 6	M 8	M 10	M 12
d <sub>k</sub> in mm	3.8	4.5	5.5	6.0	7.0	8.5	10.0	13.0	16.0	18.0
k in mm	1.3	1.6	2.0	2.4	2.6	3.3	3.9	5.0	6.0	7.0
n in mm	0.5	0.6	0.8	1.0	1.2	1.2	1.6	2.0	2.5	2.5
t in mm	0.6	0.7	0.85	1.0	1.1	1.3	1.6	2.0	2.4	2.4

### Assortments



Slotted fillister-head screws, DIN 84, steel galvanised, blue passivated, 1,350 pieces

Article:  
0040 3 x 10/16/20/25  
0040 4 x 10/16/20/25  
0040 5 x 10/20/30/40  
0040 6 x 16/20/25/30  
Deep-Drawn Part, Art. No. 0955 801 6

**Art. No. 0964 040**  
P. Qty. 1

Slotted fillister-head screws, DIN 84, stainless steel A2, 1,340 pieces

Article:  
0287 4 x 8/10/16/20  
0287 5 x 8/10/12/16/20/30  
0287 6 x 16/20/25/30/35/40  
Deep-drawn part, Art. No. 0955 801 6

**Art. No. 0964 287**  
P. Qty. 1

slotted  
according to DIN 84 (ISO 1207)

Bare brass (CuZn 37)  
Bare steel 4.8  
Galvanised steel 4.8, blue passivated  
Galvanised steel 4.8, yellow passivated  
A2   
A4

Threaded screws, DIN 963, DIN 84, galvanised, blue passivated; nuts DIN 934-8, galvanised, blue passivated; washers, DIN 125A, galvanised, blue passivated 1,200 pieces

Article:  
0039 4 x 10/5 x 16/6 x 20  
0040 4 x 10/16/20  
0040 5 x 10/16/20  
0040 6 x 16/20/25  
0317 4/5/6  
0407 4/5/6  
Deep-drawn part, Art. No. 0955 801 8

**Art. No. 0964 040 1**  
P. Qty. 1

Nominal dia. d	Length l mm	Bare brass Art. No.	P. Qty.	Bare steel 4.8 Art. No.	P. Qty.	Galv. steel 4.8 blue pass. Art. No.	P. Qty.	Galv. steel 4.8 yellow pass. Art. No.	P. Qty.	A2  Art. No.	P. Qty.	A4  Art. No.	P. Qty.
M 2	3			<b>0040 02 3</b>		<b>0040 2 3</b>	2000	<b>0040 72 3</b>					
	4	<b>0001 2 4</b>	500/2000	<b>0040 02 4</b>		<b>0040 2 4</b>		<b>0040 72 4</b>	2000	<b>0287 2 4</b>	1000		
	5	<b>0001 2 5</b>		<b>0040 02 5</b>		<b>0040 2 5</b>	100/500	<b>0040 72 5</b>		<b>0287 2 5</b>	50		
	6	<b>0001 2 6</b>		<b>0040 02 6</b>		<b>0040 2 6</b>		<b>0040 72 6</b>	500/2000	<b>0287 2 6</b>			
	8	<b>0001 2 8</b>	2000	<b>0040 02 8</b>		<b>0040 2 8</b>		<b>0040 72 8</b>		<b>0287 2 8</b>	1000		
	10	<b>0001 2 10</b>		<b>0040 02 10</b>		<b>0040 2 10</b>	500	<b>0040 72 10</b>		<b>0287 2 10</b>	500		
	12	<b>0001 2 12</b>	200	<b>0040 02 12</b>	2000	<b>0040 2 12</b>	100/500	<b>0040 72 12</b>					
	14	<b>0001 2 14</b>		<b>0040 02 14</b>		<b>0040 2 14</b>	2000		2000				
	16	<b>0001 2 16</b>		<b>0040 02 16</b>		<b>0040 2 16</b>	100/500	<b>0040 72 16</b>					
	18		2000	<b>0040 02 18</b>		<b>0040 2 18</b>	2000			<b>0287 2 18</b>	1000		
M 2.5	20	<b>0001 2 20</b>		<b>0040 02 20</b>		<b>0040 2 20</b>	100/500	<b>0040 72 20</b>					
	22	<b>0001 2 22</b>		<b>0040 02 22</b>		<b>0040 2 22</b>							
	25	<b>0001 2 25</b>		<b>0040 02 25</b>		<b>0040 2 25</b>	2000						
	30			<b>0040 02 30</b>		<b>0040 2 30</b>							
	3			<b>0040 025 3</b>		<b>0040 25 3</b>	2000			<b>0287 25 3</b>			
	4	<b>0001 25 4</b>		<b>0040 025 4</b>		<b>0040 25 4</b>		<b>0040 725 4</b>		<b>0287 25 4</b>			
	5	<b>0001 25 5</b>	2000	<b>0040 025 5</b>		<b>0040 25 5</b>	100	<b>0040 725 5</b>	2000	<b>0287 25 5</b>	1000		
	6	<b>0001 25 6</b>		<b>0040 025 6</b>		<b>0040 25 6</b>		<b>0040 725 6</b>		<b>0287 25 6</b>			
	8	<b>0001 25 8</b>	500	<b>0040 025 8</b>		<b>0040 25 8</b>	100/500	<b>0040 725 8</b>	500/2000	<b>0287 25 8</b>		<b>0289 25 8</b>	1000
	10	<b>0001 25 10</b>	2000	<b>0040 025 10</b>		<b>0040 25 10</b>		<b>0040 725 10</b>		<b>0287 25 10</b>	500		
12	<b>0001 25 12</b>	200	<b>0040 025 12</b>	2000	<b>0040 25 12</b>		<b>0040 725 12</b>	500	<b>0287 25 12</b>	100			
14	<b>0001 25 14</b>		<b>0040 025 14</b>		<b>0040 25 14</b>	2000	<b>0040 725 14</b>	2000	<b>0287 25 14</b>				
16	<b>0001 25 16</b>	2000	<b>0040 025 16</b>		<b>0040 25 16</b>	100/500	<b>0040 725 16</b>	500	<b>0287 25 16</b>	1000			
18			<b>0040 025 18</b>		<b>0040 25 18</b>	2000	<b>0040 725 18</b>	2000	<b>0287 25 18</b>	500	<b>0289 25 18</b>	2000	
20	<b>0001 25 20</b>	1000	<b>0040 025 20</b>		<b>0040 25 20</b>	100/500	<b>0040 725 20</b>	500	<b>0287 25 20</b>	200			
22			<b>0040 025 22</b>		<b>0040 25 22</b>	2000	<b>0040 725 22</b>	2000	<b>0287 25 22</b>	500			