

HEXAGON NUTS

Metric standard thread DIN 934

Std. thread d	s in mm	e in mm	m in mm	Steel I81				Steel I101					
				Bare		Galvanized, blue passivated (A2K)		Galvanized, yellow passivated (A2C)		Bare		Galvanized, yellow passivated (A2C)	
				Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.
M 1.6	3.2	3.41	1.3	-	-	-	-	-	-	-	-	-	-
M 2	4	4.32	1.6	0310 2	500	0317 2	500/1,000/10,000	-	-	-	-	-	-
M 2.5	5	5.45	2	0310 25	1,000	0317 25	500/1,000/10,000	-	-	-	-	-	-
M 3	5.5	6.01	2.4	0310 3	500/1,000/10,000	0317 3	500/1,000/2,500	0317 03	500/10,000	0320 3	1,000	0324 3	1,000
M 3.5	6	6.58	2.8	-	-	0317 35	500/5000	-	-	-	-	-	-
M 4	7	7.66	3.2	0310 4	500/1,000	0317 4	500/100	0317 04	500/1,000	0320 4	200/1,000	0324 4	1,000
M 5	8	8.79	4	0310 5	500/1,000	0317 5	100/250/500/1,000	0317 05	250/500/1,000	0320 5	100	0324 5	1,000
M 6	10	11.05	5	0310 6	500/1,000/2,000	0317 6	100/250/500/1,000	0317 06	250/500/2,000	0320 6	100/1,000	0324 6	100/1,000
M 7	11	12.12	5.5	0310 7	100	0317 7	100/1,000	0317 07	100/500	-	-	-	-
M 8	13	14.38	6.5	0310 8	100/200/1,000	0317 8	100/250/500/1,000	0317 08	100/500	0320 8	100/1,000	0324 8	100/1,000
M 8*	12	11.28	6.5	-	-	0317 8 12	100	-	-	-	-	-	-
M 10	17	18.9	8	0310 10	100/500	0317 10	100/300/500	0317 010	100/500	0320 10	100/500	0324 10	100/300/500
M 10*	15	18.4	8	-	-	0317 10 15	100	0317 010 15	100	-	-	-	-
M 12	19	21.1	10	0310 12	100/250/300	0317 12	100/250/300	0317 012	100/250/300	0320 12	100/200	0324 12	100/300
M 14	22	24.49	11	0310 14	50/250	0317 14	50/100/250	0317 014	25/100/200	0320 14	50	0324 14	50/100
M 16	24	26.75	13	0310 16	50/100/200	0317 16	50/100/200	0317 016	25/100/200	0320 16	50/100/200	0324 16	50/100
M 18	27	29.56	15	0310 18	100	0317 18	25/100	0317 018	25/100	0320 18	50/100	0324 18	50/100/200
M 20	30	32.95	16	0310 20	25/100	0317 20	25/100	0317 020	25/100	0320 20	50/100	0324 20	25/100
M 22	32	35.03	18	0310 22	25/50	0317 22	25/50	-	-	-	-	-	-
M 24	36	39.55	19	0310 24	25/50	0317 24	25/50	0317 024	-50	0320 24	25/50	0324 24	25/50
M 27	41	45.2	22	0310 27	25	0317 27	5/25	-	-	0320 27	25	-	-
M 30	46	50.85	24	0310 30	5/25	0317 30	5/25	0317 030	25	0320 30	10/25	-	-
M 33	50	55.37	26	0310 33	5/20	0317 33	1/5/20	-	-	-	-	-	-
M 36	55	60.79	29	0310 36	1/5/10	0317 36	1/5/10	0317 036	1/5/10	0320 36	10	-	-
M 42	65	71.3	34	0310 42	1/5/10	0317 42	1/5/10	0317 042	1/5/10	-	-	-	-
M 48	75	82.6	38	0310 48	1	-	-	-	-	-	-	-	-
M 52	80	88.25	42	-	-	-	-	-	-	-	-	-	-
M 60	90	99.21	48	-	-	0317 60	-	-	-	-	-	-	-

Std. thread d	s in mm	e in mm	m in mm	A2		A4		Brass Bare		Polyamide height m in mm	PA 6.6 wrench size s		
				Rost fre!		Rost fre!							
				Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.			Art. No.	P. Qty.
M 1.6	3.2	3.41	1.3	0322 15	1,000	-	-	-	-	-	-	-	-
M 2	4	4.32	1.6	0322 2	500/1,000	0326 2	1,000	0300 2	500/5000	-	-	-	-
M 2.5	5	5.45	2	0322 25	500/1,000	0326 25	1,000	0300 25	1,000	-	-	-	-
M 3	5.5	6.01	2.4	0322 3	300/1,000	0326 3	100	0300 3	300/1,000	2.15-2.4	5.5	0323 3	100/1,000
M 3.5	6	6.58	2.8	0322 35	1,000	-	-	-	-	-	-	-	-
M 4	7	7.66	3.2	0322 4	300/500	0326 4	100	0300 4	300/1,000/2,000	2.9-3.2	7.0	0323 4	100/500
M 5	8	8.79	4	0322 5	300/500	0326 5	100	0300 5	300/1,000/2,000	4.4-4.7	8.0	0323 5	100/500
M 6	10	11.05	5	0322 6	300/500	0326 6	100	0300 6	300/1,000	4.9-5.2	10.0	0323 6	100/250
M 7	11	12.12	5.5	-	-	-	-	-	-	-	-	-	-
M 8	13	14.38	6.5	0322 8	100/500	0326 8	100	0300 8	100/300/1,000	6.4-6.8	13.0	0323 8	100/250
M 8*	12	11.28	6.5	-	-	-	-	-	-	-	-	-	-
M 10	17	18.9	8	0322 10	100/500	0326 10	100	0300 10	100/500	8.04-8.4	16.0	0323 10	100
M 10*	15	18.4	8	-	-	-	-	-	-	-	-	-	-
M 12	19	21.1	10	0322 12	50/100/250	0326 12	50	0300 12	50/400	10.37-10.8	18.0	0323 12	100
M 14	22	24.49	11	0322 14	50/100	-	-	0300 14	50	-	-	-	-
M 16	24	26.75	13	0322 16	50/100/200	0326 16	50	0300 16	50/200	-	-	-	-
M 18	27	29.56	15	0322 18	50	-	-	-	-	-	-	-	-
M 20	30	32.95	16	0322 20	25/50	0326 20	25	0300 20	25/100	-	-	-	-
M 22	32	35.03	18	0322 22	5	-	-	-	-	-	-	-	-
M 24	36	39.55	19	0322 24	5/50	0326 24	5	-	-	-	-	-	-
M 27	41	45.2	22	0322 27	5/25	0326 27	5	-	-	-	-	-	-
M 30	46	50.85	24	0322 30	5/25	0326 30	5	-	-	-	-	-	-

Metric fine thread DIN 934

Fine thread d	s in mm	e in mm	m in mm	Steel I81				Steel I101					
				Bare		Galvanized, blue passivated (A2K)		Galvanized, yellow passivated (A2C)		Bare		Galvanized, blue passivated (A2C)	
				Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.
M 8 x 1	13	14.38	6.5	0310 8 113	300	0317 8 113	100	0317 08 113	100/1,000	0320 8 113	100	-	-
M 10 x 1	17	18.9	8	0310 10 1	100	0317 10 1	100/500	0317 010 1	100/500	0320 10 1	100	0324 10 1	100
M 10 x 1.25	17	18.9	8	0310 10 125	100/500	0317 10 125	100	0317 010 125	100/500	-	-	-	-
M 10 x 1.25	17	18.9	8	-	-	0317 10 141	50	0317 010 141	50	-	-	-	-
M 12 x 1.25	19	21.1	10	0310 12 125	100	0317 12 125	100	0317 012 125	50/400	0320 12 125	100/500	-	-
M 12 x 1.5	19	21.1	10	0310 12 15	100	0317 12 15	100/500	0317 012 15	50/250	0320 12 15	100/500	0324 12 15	50

*Reduced wrench size