

HEXAGON NUTS

Metric ISO 934 standard thread

Fine thread d	s in mm	e in mm	m in mm	Steel 8				Steel 10					
				Bare		Galvanized, blue passivated (A2K)		Galvanized, yellow passivated (A2C)		Bare		Galvanized, blue passivated (A2C)	
				Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.
M 30	46	50.85	25.6	0310 930	20	0317 930	25	-	-	0320 930	5/25	-	-
M 33	50	55.37	28.7	0310 933	10	-	-	-	-	-	-	-	-
M 36	55	60.79	31	0310 936	10	0317 936	15	-	-	0320 936	15	-	-
M 42	65	71.3	34	-	-	-	-	-	-	-	-	-	-
M 48	75	82.6	38	0310 948	1/5	-	-	-	-	-	-	-	-

Fine thread d	s in mm	e in mm	m in mm	A2		A4		Brass	
				Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.
M 2	4	4.32	1.6	-	-	-	-	-	-
M 2.5	5	5.45	2	-	-	-	-	-	-
M 3	5.5	6.01	2.4	0322 93	100/2,000	-	-	0300 93	2,000
M 3.5	6	6.58	2.8	-	-	-	-	-	-
M 4	7	7.66	3.2	0322 94	100/500	0326 94	1,000	0300 94	2,000
M 5	8	8.79	4.7	0322 95	100/1,000	0326 95	100/1,000	0300 95	2,000
M 6	10	11.05	5.2	0322 96	100/500/1,000	0326 96	100/1,000	0300 96	1,000
M 8	13	14.38	6.8	0322 98	100/500	0326 98	100/1,000	0300 98	1,000
M 10	16	17.77	8.4	0322 910	100/500	0326 910	100/500	0300 910	500
M 12	18	20.03	10.8	0322 912	50/100/500	0326 912	50	0300 912	500
M 14	21	23.36	12.8	0322 914	100	-	-	-	-
M 16	24	26.75	14.8	0322 916	50	0326 916	50/200	-	-
M 18	27	29.56	15.8	-	-	-	-	-	-
M 20	30	32.95	18	0322 920	50	0326 920	25	-	-
M 22	34	37.29	19.4	-	-	-	-	-	-
M 24	36	39.55	21.5	-	-	0326 924	50	-	-
M 27	41	45.2	23.8	-	-	0326 927	1	-	-
M 30	46	50.85	25.6	-	-	-	-	-	-
M 33	50	55.37	28.7	-	-	-	-	-	-
M 36	55	60.79	31	-	-	-	-	-	-
M 42	65	71.3	34	-	-	-	-	-	-
M 48	75	82.6	38	-	-	-	-	-	-

Metric ISO 4032 fine thread

Fine thread d	s in mm	e in mm	m in mm	Steel 8				Steel 10					
				Bare		Galvanized, blue passivated (A2K)		Galvanized, yellow passivated (A2C)		Bare		Galvanized, blue passivated (A2C)	
				Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.	Art. No.	P. Qty.
M 8 x 1	13	14.38	6.8	-	-	-	-	-	-	-	-	-	-
M 10 x 1	16	17.77	8.4	0310 910 1	500	0317 910 1	500	-	-	0320 910 1	500	0324 910 1	500
M 10 x 1.25	16	17.77	8.4	-	-	0317 910 125	100	-	-	-	-	-	-
M 12 x 1.25	18	20.03	10.8	0310 912 125	100	0317 912 125	50	-	-	0320 912 125	100	-	-
M 12 x 1.5	18	20.03	10.8	0310 912 15	50/250	0317 912 15	100	-	-	-	-	0324 912 15	50
M 14 x 1.5	21	23.35	12.8	-	-	0317 914 15	200	0317 814 15	200	-	-	-	-
M 16 x 1.5	24	26.75	14.8	-	-	0317 916 15	100	0317 816 15	200	-	-	-	-
M 18 x 1.5	27	29.56	15.8	0310 918 15	100	-	-	0317 818 15	100	-	-	-	-
M 18 x 2	27	29.56	15.8	-	-	-	-	-	-	-	-	-	-
M 20 x 1.5	30	32.95	18	-	-	-	-	-	-	0320 920 15	50/100	0324 920 15	100
M 20 x 2	30	32.95	18	-	-	-	-	-	-	-	-	-	-
M 22 x 1.5	34	37.29	19.4	-	-	-	-	-	-	-	-	-	-
M 22 x 2	34	37.29	19.4	-	-	-	-	-	-	-	-	-	-
M 24 x 1.5	36	39.55	21.5	0310 924 15	50	-	-	-	-	-	-	-	-
M 24 x 2	36	39.55	21.5	-	-	-	-	-	-	-	-	-	-
M 30 x 1.5	46	50.85	25.6	-	-	-	-	-	-	-	-	-	-
M 30 x 2	46	50.85	25.6	-	-	-	-	-	-	-	-	-	-