

Zebra Screwdriver with end-to-end hexagon blade/spanner nut of special impact resistant tempered steel.



Slotted Screwdriver

Blade: End-to-end hexagon blade with spanner nut from 0.8x4.5 mm, nicromatt, impact resistant, tempered steel.

Big striking cap.

Drive: DIN 5264-A, ISO 2380
Black Point.

* without striking cap/spanner nut

 a mm	 A mm B/C mm		 mm	 b inch A	Art. No.	
	A mm	B/C mm				
0.6 x 3.5	80	83/27	4/-	1/8 x 3 1/16"	0613 421 035*	1
0.8 x 4.5	90	96/31	5/8	3/16 x 3 3/5"	0613 321 045	
1.0 x 5.5	100	96/31	6/10	7/32 x 4"	0613 321 055	
1.2 x 7.0	125	106/35	6/10	9/32 x 5"	0613 321 07	
1.6 x 9.0	150	114/38	8/13	11/32 x 6"	0613 321 09	
1.6 x 10.0	175	114/38	8/13	3/8 x 7"	0613 321 10	
2.0 x 12.0	200	120/40.5	10/16	1/2 x 8"	0613 321 12	
2.5 x 14.0	250	120/40.5	10/16	9/16 x 10"	0613 321 14	



Screwdriver Cross-recess (PH)

Blade: End-to-end hexagon blade with spanner nut, nicromatt, impact resistant, tempered steel.

Big striking cap.

Drive: DIN 5260-PH, ISO 8764-PH
Black Point.

	 A mm B/C mm		 mm	 A inch	Art. No.	
	A mm	B/C mm				
PH1	80	96/31	5/8	3 1/8"	0613 322 1	1
PH2	100	106/35	6/10	4"	0613 322 2	
PH3	150	114/38	8/13	6"	0613 322 3	
PH4	200	120/40,5	10/16	8"	0613 322 4	



Set of Screwdrivers for the automotive and the metal working trade

Art. No. 0613 932 25

	Art. No.		Art. No.	
1.0 x 5.5 x 100	0613 321 055	PH1	0613 322 1	1
1.2 x 7.0 x 125	0613 321 07	PH2	0613 322 2	
1.6 x 9.0 x 150	0613 321 09			