

SPADE DRILLS



Diameter	Length	Shank diameter	Material	Art. No.	P. Qty.
6 mm	150 mm	1/4 in	Hardened steel	0650 007 006	1
8 mm	150 mm	1/4 in	Hardened steel	0650 007 008	1
8 mm	400 mm	1/4 in	Hardened steel	0650 008 008	1
10 mm	150 mm	1/4 in	Hardened steel	0650 007 010	1
10 mm	400 mm	1/4 in	Hardened steel	0650 008 010	1
12 mm	150 mm	1/4 in	Hardened steel	0650 007 012	1
12 mm	400 mm	1/4 in	Hardened steel	0650 008 012	1
14 mm	150 mm	1/4 in	Hardened steel	0650 007 014	1
14 mm	400 mm	1/4 in	Hardened steel	0650 008 014	1
16 mm	150 mm	1/4 in	Hardened steel	0650 007 016	1
16 mm	400 mm	1/4 in	Hardened steel	0650 008 016	1
18 mm	150 mm	1/4 in	Hardened steel	0650 007 018	1
18 mm	400 mm	1/4 in	Hardened steel	0650 008 018	1
20 mm	150 mm	1/4 in	Hardened steel	0650 007 020	1
20 mm	400 mm	1/4 in	Hardened steel	0650 008 020	1
22 mm	150 mm	1/4 in	Hardened steel	0650 007 022	1
22 mm	400 mm	1/4 in	Hardened steel	0650 008 022	1
25 mm	150 mm	1/4 in	Hardened steel	0650 007 025	1
26 mm	152 mm	1/4 in	Hardened steel	0650 007 026	1
26 mm	400 mm	1/4 in	Hardened steel	0650 008 026	1
30 mm	150 mm	1/4 in	Hardened steel	0650 007 030	1
30 mm	400 mm	1/4 in	Hardened steel	0650 008 030	1
32 mm	150 mm	1/4 in	Hardened steel	0650 007 032	1
35 mm	150 mm	1/4 in	Hardened steel	0650 007 035	1
35 mm	400 mm	1/4 in	Hardened steel	0650 008 035	1
40 mm	150 mm	1/4 in	Hardened steel	0650 007 040	1

Application

Medium hardwoods, soft woods, fiberboard, particle board and soft building materials, e.g. gypsum plasterboard

For wood. Drills up to 10 times faster than a standard spade drill.

Self-propelled threaded tip

Drives itself through the wood very quickly with a minimal application of force.

Two cutting edges

Fast penetration of the material with simultaneous high drilled hole quality.

Optimum, fast chip removal

Specially curved blade cleans the drilled hole before a tear-out can occur.

Hexagon shank

No slipping of drill in chuck.

SPADE DRILL ASSORTMENT

Art. No.	0650 007 004
P. Qty.	1
Number of parts in assortment/set	6 pcs.
Scope of delivery	10.0 12.0 16.0 18.0 20.0 and 25 mm dia.
Material	Hardened steel



For wood. 6 pcs. Drills up to 10 times faster than a standard spade drill.