


Countersunk tapping screw shape C with H recessed head

DIN 7982 galvanised steel, blue passivated (A2K), shape C, H recessed head.

- Self-tapping screws are screws that form their own thread. These screws form their own counter thread when screwed into a prefabricated core hole.
- Reference values for selecting the correct core-hole diameter are included in DIN 7975.
- Shape C = thread with tip



Material	Steel
Surface	Zinc plated
RoHS-compliant	Yes
Form	C



Nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive	Art. no.	P. Qty.
2.2 mm	4.5 mm	4.3 mm	1.3 mm	H1	0116 22 45	2000
2.2 mm	6.5 mm	4.3 mm	1.3 mm	H1	0116 22 65	100/5000
2.2 mm	9.5 mm	4.3 mm	1.3 mm	H1	0116 22 95	100/2000
2.2 mm	13 mm	4.3 mm	1.3 mm	H1	0116 22 13	2000
2.2 mm	16 mm	4.3 mm	1.3 mm	H1	0116 22 16	2000
2.9 mm	6.5 mm	5.5 mm	1.7 mm	H1	0116 29 65	1000 /5000
2.9 mm	8 mm	5.5 mm	1.7 mm	H1	0116 29 8	2000
2.9 mm	9.5 mm	5.5 mm	1.7 mm	H1	0116 29 95	100/1000 /5000
2.9 mm	13 mm	5.5 mm	1.7 mm	H1	0116 29 13	1000 /2000
2.9 mm	16 mm	5.5 mm	1.7 mm	H1	0116 29 16	1000 /2000
2.9 mm	19 mm	5.5 mm	1.7 mm	H1	0116 29 19	1000
2.9 mm	22 mm	5.5 mm	1.7 mm	H1	0116 29 22	1000 /2000
2.9 mm	25 mm	5.5 mm	1.7 mm	H1	0116 29 25	1000
2.9 mm	32 mm	5.5 mm	1.7 mm	H1	0116 29 32	2000
3.5 mm	9.5 mm	6.8 mm	2.1 mm	H2	0116 35 95	300/1000 /2000
3.5 mm	13 mm	6.8 mm	2.1 mm	H2	0116 35 13	300/1000 /2000
3.5 mm	16 mm	6.8 mm	2.1 mm	H2	0116 35 16	300/1000 /2000
3.5 mm	19 mm	6.8 mm	2.1 mm	H2	0116 35 19	300/1000 /2000
3.5 mm	22 mm	6.8 mm	2.1 mm	H2	0116 35 22	1000
3.5 mm	25 mm	6.8 mm	2.1 mm	H2	0116 35 25	100/1000 /2000
3.5 mm	32 mm	6.8 mm	2.1 mm	H2	0116 35 32	1000

Nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive	Art. no.	P. Qty.
3.5 mm	38 mm	6.8 mm	2.1 mm	H2	0116 35 38	1000
3.9 mm	9.5 mm	7.5 mm	2.3 mm	H2	0116 39 95	1000 /2000
3.9 mm	13 mm	7.5 mm	2.3 mm	H2	0116 39 13	1000 /2000
3.9 mm	16 mm	7.5 mm	2.3 mm	H2	0116 39 16	1000 /2500
3.9 mm	19 mm	7.5 mm	2.3 mm	H2	0116 39 19	100/1000 /2000
3.9 mm	22 mm	7.5 mm	2.3 mm	H2	0116 39 22	300/1000
3.9 mm	25 mm	7.5 mm	2.3 mm	H2	0116 39 25	100/300 /1000 /2000
3.9 mm	32 mm	7.5 mm	2.3 mm	H2	0116 39 32	100/1000 /2000
3.9 mm	38 mm	7.5 mm	2.3 mm	H2	0116 39 38	100/1000
3.9 mm	45 mm	7.5 mm	2.3 mm	H2	0116 39 45	100/1000
3.9 mm	50 mm	7.5 mm	2.3 mm	H2	0116 39 50	1000
4.2 mm	9.5 mm	8.1 mm	2.5 mm	H2	0116 42 95	100/2000
4.2 mm	13 mm	8.1 mm	2.5 mm	H2	0116 42 13	1000
4.2 mm	16 mm	8.1 mm	2.5 mm	H2	0116 42 16	300/1000 /2000
4.2 mm	19 mm	8.1 mm	2.5 mm	H2	0116 42 19	300/1000 /2000
4.2 mm	22 mm	8.1 mm	2.5 mm	H2	0116 42 22	1000
4.2 mm	25 mm	8.1 mm	2.5 mm	H2	0116 42 25	100/1000 /2000
4.2 mm	32 mm	8.1 mm	2.5 mm	H2	0116 42 32	100/1000
4.2 mm	38 mm	8.1 mm	2.5 mm	H2	0116 42 38	100/1000
4.2 mm	45 mm	8.1 mm	2.5 mm	H2	0116 42 45	1000
4.2 mm	50 mm	8.1 mm	2.5 mm	H2	0116 42 50	1000
4.2 mm	60 mm	8.1 mm	2.5 mm	H2	0116 42 60	100
4.2 mm	70 mm	8.1 mm	2.5 mm	H2	0116 42 70	100
4.2 mm	80 mm	8.1 mm	2.5 mm	H2	0116 42 80	500
4.8 mm	9.5 mm	9.5 mm	3 mm	H2	0116 48 95	100/500
4.8 mm	13 mm	9.5 mm	3 mm	H2	0116 48 13	100/1000 /2000
4.8 mm	16 mm	9.5 mm	3 mm	H2	0116 48 16	300/1000
4.8 mm	19 mm	9.5 mm	3 mm	H2	0116 48 19	100/1000 /2000
4.8 mm	22 mm	9.5 mm	3 mm	H2	0116 48 22	100/1000 /2000
4.8 mm	25 mm	9.5 mm	3 mm	H2	0116 48 25	100/1000
4.8 mm	32 mm	9.5 mm	3 mm	H2	0116 48 32	100/1000
4.8 mm	35 mm	9.5 mm	3 mm	H2	0116 48 35	2000
4.8 mm	38 mm	9.5 mm	3 mm	H2	0116 48 38	100/500 /1000
4.8 mm	45 mm	9.5 mm	3 mm	H2	0116 48 45	100/500
4.8 mm	50 mm	9.5 mm	3 mm	H2	0116 48 50	100/500 /1000
4.8 mm	60 mm	9.5 mm	3 mm	H2	0116 48 60	100/500
4.8 mm	70 mm	9.5 mm	3 mm	H2	0116 48 70	100/200 /500
4.8 mm	80 mm	9.5 mm	3 mm	H2	0116 48 80	100
4.8 mm	90 mm	9.5 mm	3 mm	H2	0116 48 90	100/200
4.8 mm	100 mm	9.5 mm	3 mm	H2	0116 48 100	100

Nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive	Art. no.	P. Qty.
4.8 mm	110 mm	9.5 mm	3 mm	H2	0116 48 110	100
4.8 mm	120 mm	9.5 mm	3 mm	H2	0116 48 120	100/200
4.8 mm	160 mm	9.5 mm	3 mm	H2	0116 48 160	100
5.5 mm	13 mm	10.8 mm	3.4 mm	H3	0116 55 13	100/1000
5.5 mm	16 mm	10.8 mm	3.4 mm	H3	0116 55 16	100/500
5.5 mm	19 mm	10.8 mm	3.4 mm	H3	0116 55 19	100/500
5.5 mm	22 mm	10.8 mm	3.4 mm	H3	0116 55 22	100
5.5 mm	25 mm	10.8 mm	3.4 mm	H3	0116 55 25	100/2000
5.5 mm	32 mm	10.8 mm	3.4 mm	H3	0116 55 32	100/500
5.5 mm	38 mm	10.8 mm	3.4 mm	H3	0116 55 38	100
5.5 mm	45 mm	10.8 mm	3.4 mm	H3	0116 55 45	100
5.5 mm	50 mm	10.8 mm	3.4 mm	H3	0116 55 50	100/600
5.5 mm	60 mm	10.8 mm	3.4 mm	H3	0116 55 60	100/250
5.5 mm	70 mm	10.8 mm	3.4 mm	H3	0116 55 70	100
5.5 mm	80 mm	10.8 mm	3.4 mm	H3	0116 55 80	100
5.5 mm	90 mm	10.8 mm	3.4 mm	H3	0116 55 90	100
5.5 mm	100 mm	10.8 mm	3.4 mm	H3	0116 55 100	100
5.5 mm	110 mm	10.8 mm	3.4 mm	H3	0116 55 110	100
5.5 mm	120 mm	10.8 mm	3.4 mm	H3	0116 55 120	100
6.3 mm	13 mm	12.4 mm	3.8 mm	H3	0116 63 13	3000
6.3 mm	16 mm	12.4 mm	3.8 mm	H3	0116 63 16	100
6.3 mm	19 mm	12.4 mm	3.8 mm	H3	0116 63 19	100/500
6.3 mm	22 mm	12.4 mm	3.8 mm	H3	0116 63 22	100
6.3 mm	25 mm	12.4 mm	3.8 mm	H3	0116 63 25	100/500
6.3 mm	32 mm	12.4 mm	3.8 mm	H3	0116 63 32	100/1000
6.3 mm	38 mm	12.4 mm	3.8 mm	H3	0116 63 38	100
6.3 mm	45 mm	12.4 mm	3.8 mm	H3	0116 63 45	100
6.3 mm	50 mm	12.4 mm	3.8 mm	H3	0116 63 50	100/500
6.3 mm	60 mm	12.4 mm	3.8 mm	H3	0116 63 60	100/200
6.3 mm	70 mm	12.4 mm	3.8 mm	H3	0116 63 70	100
6.3 mm	80 mm	12.4 mm	3.8 mm	H3	0116 63 80	100
6.3 mm	90 mm	12.4 mm	3.8 mm	H3	0116 63 90	100
6.3 mm	100 mm	12.4 mm	3.8 mm	H3	0116 63 100	100
6.3 mm	110 mm	12.4 mm	3.8 mm	H3	0116 63 110	100
6.3 mm	120 mm	12.4 mm	3.8 mm	H3	0116 63 120	100

Compatible with ORSY storage system