



Slotted cheese head

DIN 84, steel 4.8, galvanised, blue passivated (A2K)

Internal drive	Slot
Standards	DIN 84
Material	Steel
Property class	4.8
Surface	Zinc plated
RoHS-compliant	Yes



Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Art. no.	P. Qty.
M1	5 mm	2 mm	0.7 mm	0040 1 5	200
M1.4	4 mm	2.6 mm	0.9 mm	0040 14 4	100
M1.6	2 mm	3 mm	1 mm	0040 16 2	2000
M1.6	3 mm	3 mm	1 mm	0040 16 3	500
M1.6	4 mm	3 mm	1 mm	0040 16 4	100
M1.6	5 mm	3 mm	1 mm	0040 16 5	2000
M1.6	8 mm	3 mm	1 mm	0040 16 8	500
M1.6	12 mm	3 mm	1 mm	0040 16 12	500
M1.6	16 mm	3 mm	1 mm	0040 16 16	500
M1.7	4 mm	3.2 mm	1.1 mm	0040 17 4	1000
M2	2 mm	3.8 mm	1.3 mm	0040 2 2	500
M2	3 mm	3.8 mm	1.3 mm	0040 2 3	2000
M2	4 mm	3.8 mm	1.3 mm	0040 2 4	500/2000
M2	5 mm	3.8 mm	1.3 mm	0040 2 5	500/2000
M2	6 mm	3.8 mm	1.3 mm	0040 2 6	500/2000
M2	8 mm	3.8 mm	1.3 mm	0040 2 8	500/2000
M2	10 mm	3.8 mm	1.3 mm	0040 2 10	500/2000
M2	12 mm	3.8 mm	1.3 mm	0040 2 12	500/2000
M2	14 mm	3.8 mm	1.3 mm	0040 2 14	2000
M2	16 mm	3.8 mm	1.3 mm	0040 2 16	500/2000
M2	18 mm	3.8 mm	1.3 mm	0040 2 18	2000
M2	20 mm	3.8 mm	1.3 mm	0040 2 20	500
M2	22 mm	3.8 mm	1.3 mm	0040 2 22	2000
M2	25 mm	3.8 mm	1.3 mm	0040 2 25	2000
M2	30 mm	3.8 mm	1.3 mm	0040 2 30	2000
M2.3	6 mm	4.4 mm	1.5 mm	0040 23 6	500
M2.3	12 mm	4.4 mm	1.5 mm	0040 23 12	100
M2.5	3 mm	4.5 mm	1.6 mm	0040 25 3	2000
M2.5	4 mm	4.5 mm	1.6 mm	0040 25 4	100
M2.5	5 mm	4.5 mm	1.6 mm	0040 25 5	100/2000
M2.5	6 mm	4.5 mm	1.6 mm	0040 25 6	500/2000
M2.5	8 mm	4.5 mm	1.6 mm	0040 25 8	500/6000
M2.5	10 mm	4.5 mm	1.6 mm	0040 25 10	500/2000
M2.5	12 mm	4.5 mm	1.6 mm	0040 25 12	500/2000
M2.5	14 mm	4.5 mm	1.6 mm	0040 25 14	2000

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Art. no.	P. Qty.
M2.5	16 mm	4.5 mm	1.6 mm	0040 25 16	500
M2.5	18 mm	4.5 mm	1.6 mm	0040 25 18	2000
M2.5	20 mm	4.5 mm	1.6 mm	0040 25 20	500
M2.5	22 mm	4.5 mm	1.6 mm	0040 25 22	2000
M2.5	25 mm	4.5 mm	1.6 mm	0040 25 25	100
M2.5	28 mm	4.5 mm	1.6 mm	0040 25 28	2000
M2.5	30 mm	4.5 mm	1.6 mm	0040 25 30	2000
M2.5	40 mm	4.5 mm	1.6 mm	0040 25 40	1000
M3	3 mm	5.5 mm	2 mm	0040 3 3	2000
M3	4 mm	5.5 mm	2 mm	0040 3 4	500/2000
M3	5 mm	5.5 mm	2 mm	0040 3 5	500/2000
M3	6 mm	5.5 mm	2 mm	0040 3 6	1000 /2000
M3	8 mm	5.5 mm	2 mm	0040 3 8	500/2000
M3	10 mm	5.5 mm	2 mm	0040 3 10	500/2000
M3	12 mm	5.5 mm	2 mm	0040 3 12	500/2000
M3	14 mm	5.5 mm	2 mm	0040 3 14	2000
M3	15 mm	5.5 mm	2 mm	0040 3 15	1000
M3	16 mm	5.5 mm	2 mm	0040 3 16	500/2000
M3	18 mm	5.5 mm	2 mm	0040 3 18	100/2000
M3	20 mm	5.5 mm	2 mm	0040 3 20	500/2000
M3	22 mm	5.5 mm	2 mm	0040 3 22	2000
M3	25 mm	5.5 mm	2 mm	0040 3 25	500/2000
M3	28 mm	5.5 mm	2 mm	0040 3 28	2000
M3	30 mm	5.5 mm	2 mm	0040 3 30	500/2000
M3	32 mm	5.5 mm	2 mm	0040 3 32	1000
M3	33 mm	5.5 mm	2 mm	0040 3 33	1000
M3	35 mm	5.5 mm	2 mm	0040 3 35	1000 /2000
M3	38 mm	5.5 mm	2 mm	0040 3 38	2000
M3	40 mm	5.5 mm	2 mm	0040 3 40	1000
M3	45 mm	5.5 mm	2 mm	0040 3 45	100/1000
M3	50 mm	5.5 mm	2 mm	0040 3 50	250/1000
M3	55 mm	5.5 mm	2 mm	0040 3 55	500
M3	60 mm	5.5 mm	2 mm	0040 3 60	250
M3	65 mm	5.5 mm	2 mm	0040 3 65	100
M3	70 mm	5.5 mm	2 mm	0040 3 70	500
M3	80 mm	5.5 mm	2 mm	0040 3 80	100
M3.5	5 mm	6 mm	2.4 mm	0040 35 5	2000
M3.5	6 mm	6 mm	2.4 mm	0040 35 6	2000
M3.5	8 mm	6 mm	2.4 mm	0040 35 8	2000
M3.5	10 mm	6 mm	2.4 mm	0040 35 10	2000
M3.5	12 mm	6 mm	2.4 mm	0040 35 12	2000
M3.5	14 mm	6 mm	2.4 mm	0040 35 14	2000
M3.5	16 mm	6 mm	2.4 mm	0040 35 16	2000
M3.5	18 mm	6 mm	2.4 mm	0040 35 18	2000
M3.5	20 mm	6 mm	2.4 mm	0040 35 20	2000
M3.5	22 mm	6 mm	2.4 mm	0040 35 22	2000
M3.5	25 mm	6 mm	2.4 mm	0040 35 25	2000
M3.5	28 mm	6 mm	2.4 mm	0040 35 28	2000
M3.5	30 mm	6 mm	2.4 mm	0040 35 30	1000
M3.5	32 mm	6 mm	2.4 mm	0040 35 32	1000
M3.5	35 mm	6 mm	2.4 mm	0040 35 35	1000
M3.5	38 mm	6 mm	2.4 mm	0040 35 38	1000

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Art. no.	P. Qty.
M3.5	40 mm	6 mm	2.4 mm	0040 35 40	1000
M3.5	42 mm	6 mm	2.4 mm	0040 35 42	500
M3.5	45 mm	6 mm	2.4 mm	0040 35 45	1000
M3.5	50 mm	6 mm	2.4 mm	0040 35 50	1000
M3.5	55 mm	6 mm	2.4 mm	0040 35 55	500
M3.5	58 mm	6 mm	2.4 mm	0040 35 58	500
M3.5	60 mm	6 mm	2.4 mm	0040 35 60	500
M3.5	65 mm	6 mm	2.4 mm	0040 35 65	500
M4	4 mm	7 mm	2.6 mm	0040 4 4	500
M4	5 mm	7 mm	2.6 mm	0040 4 5	500/2000
M4	6 mm	7 mm	2.6 mm	0040 4 6	500/2000
M4	8 mm	7 mm	2.6 mm	0040 4 8	500/2000
M4	10 mm	7 mm	2.6 mm	0040 4 10	250/1000 /2000
M4	12 mm	7 mm	2.6 mm	0040 4 12	250/2000
M4	14 mm	7 mm	2.6 mm	0040 4 14	2000
M4	16 mm	7 mm	2.6 mm	0040 4 16	250/1000 /2000
M4	18 mm	7 mm	2.6 mm	0040 4 18	2000
M4	20 mm	7 mm	2.6 mm	0040 4 20	250/1000
M4	22 mm	7 mm	2.6 mm	0040 4 22	2000
M4	25 mm	7 mm	2.6 mm	0040 4 25	250/1000
M4	28 mm	7 mm	2.6 mm	0040 4 28	1000
M4	30 mm	7 mm	2.6 mm	0040 4 30	250/1000
M4	32 mm	7 mm	2.6 mm	0040 4 32	2000
M4	35 mm	7 mm	2.6 mm	0040 4 35	250/1000
M4	38 mm	7 mm	2.6 mm	0040 4 38	2000
M4	40 mm	7 mm	2.6 mm	0040 4 40	250/1000
M4	45 mm	7 mm	2.6 mm	0040 4 45	250/1000
M4	50 mm	7 mm	2.6 mm	0040 4 50	250/1000
M4	55 mm	7 mm	2.6 mm	0040 4 55	500
M4	60 mm	7 mm	2.6 mm	0040 4 60	100/500
M4	65 mm	7 mm	2.6 mm	0040 4 65	500
M4	70 mm	7 mm	2.6 mm	0040 4 70	100/500
M4	75 mm	7 mm	2.6 mm	0040 4 75	500
M4	80 mm	7 mm	2.6 mm	0040 4 80	100/300
M4	85 mm	7 mm	2.6 mm	0040 4 85	200
M4	90 mm	7 mm	2.6 mm	0040 4 90	100
M4	100 mm	7 mm	2.6 mm	0040 4 100	100
M4	110 mm	7 mm	2.6 mm	0040 4 110	50
M5	5 mm	8.5 mm	3.3 mm	0040 5 5	250/2000
M5	6 mm	8.5 mm	3.3 mm	0040 5 6	100/1000 /2000
M5	8 mm	8.5 mm	3.3 mm	0040 5 8	100/250 /2000
M5	10 mm	8.5 mm	3.3 mm	0040 5 10	100/1000
M5	12 mm	8.5 mm	3.3 mm	0040 5 12	100/1000 /2000
M5	14 mm	8.5 mm	3.3 mm	0040 5 14	1000
M5	16 mm	8.5 mm	3.3 mm	0040 5 16	100/1000
M5	18 mm	8.5 mm	3.3 mm	0040 5 18	100/1000
M5	20 mm	8.5 mm	3.3 mm	0040 5 20	100/1000
M5	22 mm	8.5 mm	3.3 mm	0040 5 22	1000
M5	25 mm	8.5 mm	3.3 mm	0040 5 25	100/1000

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Art. no.	P. Qty.
M5	28 mm	8.5 mm	3.3 mm	0040 5 28	1000
M5	30 mm	8.5 mm	3.3 mm	0040 5 30	50/100 /1000
M5	32 mm	8.5 mm	3.3 mm	0040 5 32	500
M5	35 mm	8.5 mm	3.3 mm	0040 5 35	100/1000
M5	38 mm	8.5 mm	3.3 mm	0040 5 38	500
M5	40 mm	8.5 mm	3.3 mm	0040 5 40	50/100 /500
M5	45 mm	8.5 mm	3.3 mm	0040 5 45	100/500
M5	50 mm	8.5 mm	3.3 mm	0040 5 50	100/500
M5	55 mm	8.5 mm	3.3 mm	0040 5 55	100/500
M5	60 mm	8.5 mm	3.3 mm	0040 5 60	100/400
M5	65 mm	8.5 mm	3.3 mm	0040 5 65	100/500
M5	70 mm	8.5 mm	3.3 mm	0040 5 70	100/200
M5	75 mm	8.5 mm	3.3 mm	0040 5 75	100
M5	80 mm	8.5 mm	3.3 mm	0040 5 80	100/200
M5	85 mm	8.5 mm	3.3 mm	0040 5 85	400
M5	90 mm	8.5 mm	3.3 mm	0040 5 90	200
M5	95 mm	8.5 mm	3.3 mm	0040 5 95	100
M5	100 mm	8.5 mm	3.3 mm	0040 5 100	100
M6	6 mm	10 mm	3.9 mm	0040 6 6	500/1000
M6	8 mm	10 mm	3.9 mm	0040 6 8	500/2000
M6	10 mm	10 mm	3.9 mm	0040 6 10	250/1000
M6	12 mm	10 mm	3.9 mm	0040 6 12	250/1000
M6	14 mm	10 mm	3.9 mm	0040 6 14	1000
M6	16 mm	10 mm	3.9 mm	0040 6 16	250/1000
M6	18 mm	10 mm	3.9 mm	0040 6 18	1000
M6	20 mm	10 mm	3.9 mm	0040 6 20	250/1000
M6	22 mm	10 mm	3.9 mm	0040 6 22	500
M6	25 mm	10 mm	3.9 mm	0040 6 25	250/500
M6	28 mm	10 mm	3.9 mm	0040 6 28	500
M6	30 mm	10 mm	3.9 mm	0040 6 30	250/500
M6	32 mm	10 mm	3.9 mm	0040 6 32	500
M6	35 mm	10 mm	3.9 mm	0040 6 35	100/500
M6	38 mm	10 mm	3.9 mm	0040 6 38	500
M6	40 mm	10 mm	3.9 mm	0040 6 40	100/500
M6	45 mm	10 mm	3.9 mm	0040 6 45	100/500
M6	50 mm	10 mm	3.9 mm	0040 6 50	100/200
M6	55 mm	10 mm	3.9 mm	0040 6 55	200
M6	60 mm	10 mm	3.9 mm	0040 6 60	100/200
M6	65 mm	10 mm	3.9 mm	0040 6 65	100
M6	70 mm	10 mm	3.9 mm	0040 6 70	100/200
M6	75 mm	10 mm	3.9 mm	0040 6 75	200
M6	80 mm	10 mm	3.9 mm	0040 6 80	100/200
M6	85 mm	10 mm	3.9 mm	0040 6 85	500
M6	90 mm	10 mm	3.9 mm	0040 6 90	100
M6	95 mm	10 mm	3.9 mm	0040 6 95	100
M6	100 mm	10 mm	3.9 mm	0040 6 100	50/100
M8	10 mm	13 mm	5 mm	0040 8 10	100
M8	12 mm	13 mm	5 mm	0040 8 12	100/500
M8	14 mm	13 mm	5 mm	0040 8 14	500
M8	16 mm	13 mm	5 mm	0040 8 16	100/500
M8	18 mm	13 mm	5 mm	0040 8 18	500
M8	20 mm	13 mm	5 mm	0040 8 20	100/500

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Art. no.	P. Qty.
M8	22 mm	13 mm	5 mm	0040 8 22	500
M8	25 mm	13 mm	5 mm	0040 8 25	100/200
M8	28 mm	13 mm	5 mm	0040 8 28	200
M8	30 mm	13 mm	5 mm	0040 8 30	100/200
M8	32 mm	13 mm	5 mm	0040 8 32	200
M8	35 mm	13 mm	5 mm	0040 8 35	100
M8	38 mm	13 mm	5 mm	0040 8 38	200
M8	40 mm	13 mm	5 mm	0040 8 40	100/200
M8	45 mm	13 mm	5 mm	0040 8 45	100
M8	50 mm	13 mm	5 mm	0040 8 50	100
M8	55 mm	13 mm	5 mm	0040 8 55	100
M8	60 mm	13 mm	5 mm	0040 8 60	50
M8	65 mm	13 mm	5 mm	0040 8 65	100
M8	70 mm	13 mm	5 mm	0040 8 70	100
M8	75 mm	13 mm	5 mm	0040 8 75	100
M8	80 mm	13 mm	5 mm	0040 8 80	100
M8	85 mm	13 mm	5 mm	0040 8 85	100
M8	90 mm	13 mm	5 mm	0040 8 90	100
M8	100 mm	13 mm	5 mm	0040 8 100	100
M10	12 mm	16 mm	6 mm	0040 10 12	200
M10	14 mm	16 mm	6 mm	0040 10 14	200
M10	16 mm	16 mm	6 mm	0040 10 16	100
M10	18 mm	16 mm	6 mm	0040 10 18	200
M10	22 mm	16 mm	6 mm	0040 10 22	200
M10	25 mm	16 mm	6 mm	0040 10 25	200
M10	28 mm	16 mm	6 mm	0040 10 28	200
M10	30 mm	16 mm	6 mm	0040 10 30	200
M10	32 mm	16 mm	6 mm	0040 10 32	200
M10	35 mm	16 mm	6 mm	0040 10 35	100
M10	40 mm	16 mm	6 mm	0040 10 40	100
M10	45 mm	16 mm	6 mm	0040 10 45	100
M10	50 mm	16 mm	6 mm	0040 10 50	100
M10	55 mm	16 mm	6 mm	0040 10 55	100
M10	60 mm	16 mm	6 mm	0040 10 60	100
M10	65 mm	16 mm	6 mm	0040 10 65	100
M10	70 mm	16 mm	6 mm	0040 10 70	100
M10	75 mm	16 mm	6 mm	0040 10 75	100
M10	80 mm	16 mm	6 mm	0040 10 80	100
M10	90 mm	16 mm	6 mm	0040 10 90	100
M10	100 mm	16 mm	6 mm	0040 10 100	50
M12	20 mm	18 mm	7 mm	0040 12 20	500
M12	25 mm	18 mm	7 mm	0040 12 25	200
M12	30 mm	18 mm	7 mm	0040 12 30	500
M12	35 mm	18 mm	7 mm	0040 12 35	500
M12	40 mm	18 mm	7 mm	0040 12 40	500
M12	45 mm	18 mm	7 mm	0040 12 45	500
M12	50 mm	18 mm	7 mm	0040 12 50	500
M12	55 mm	18 mm	7 mm	0040 12 55	500
M12	60 mm	18 mm	7 mm	0040 12 60	500
M12	70 mm	18 mm	7 mm	0040 12 70	50
M12	80 mm	18 mm	7 mm	0040 12 80	50

Notice

DIN 84 has been withdrawn and replaced by ISO 1207. There is some limited similarity (nominal $\varnothing < M1.8$ removed | some head heights and head diameters changed | thread lengths changed | slot dimensions changed | some nominal diameters removed | strength class 8.8 removed).