

Blade receptacle

Uninsulated

Design	Unsealed
Material	Brass




Illustration only

Min./max. wire cross section	Nominal size of flat plug/push connector/blade connector	Number of locking lugs	Retaining-lug diameter (Ø)	Surface	Art. no.	P. Qty.
0.5-2 mm ²	6 x 0.8 mm			Tin plated	0558 190 30	25
0.5-1.5 mm ²	7.7 x 0.8 mm	1 PCS		Plain	0558 502 0	50
0.5-1 mm ²	2.8 x 0.5 mm			Plain	0558 502 9	100
0.5-1 mm ²	2.8 x 0.5 mm			Tin plated	0558 992 2	100
0.5-1 mm ²	2.8 x 0.5 mm	1 PCS		Plain	0558 601 0	100
0.5-1 mm ²	2.8 x 0.5 mm	1 PCS		Tin plated	0558 995 5	100
0.5-1 mm ²	2.8 x 0.8 mm			Tin plated	0558 992 3	100
0.5-1 mm ²	6.3 x 0.8 mm		1.4 mm	Plain	0558 504 0	100
0.5-1 mm ²	6.3 x 0.8 mm		1.4 mm	Tin plated	0558 991 9	100
0.5-1 mm ²	6.3 x 0.8 mm	1 PCS		Silver plated	0558 992 45	100
0.5-1 mm ²	6.3 x 0.8 mm	1 PCS		Tin plated	0558 991 6	100
1-1.5 mm ²	2.8 x 0.5 mm	1 PCS		Plain	0558 603 21	100
1.5-2.5 mm ²	4.8 x 0.5 mm		1.3 mm	Tin plated	0558 992 1	100
1.5-2.5 mm ²	4.8 x 0.8 mm		1.3 mm	Plain	0558 531 2	100
1.5-2.5 mm ²	4.8 x 0.8 mm	1 PCS		Plain	0558 631 2	100
1.5-2.5 mm ²	6.3 x 0.8 mm		1.4 mm	Plain	0558 450 40	100
1.5-2.5 mm ²	6.3 x 0.8 mm		1.4 mm	Plain	0558 929	100/500
1.5-2.5 mm ²	6.3 x 0.8 mm		1.4 mm	Silver plated	0558 992 5	100
1.5-2.5 mm ²	6.3 x 0.8 mm	1 PCS	1.4 mm	Plain	0558 603 2	100/300/500
1.5-2.5 mm ²	6.3 x 0.8 mm	1 PCS	1.6 mm	Silver plated	0558 992 8	100
1.5-2.5 mm ²	6.3 x 0.8 mm	1 PCS	1.6 mm	Tin plated	0558 991 7	100
4-6 mm ²	6.3 x 0.8 mm		1.4 mm	Plain	0558 504 7	100
4-6 mm ²	6.3 x 0.8 mm		1.4 mm	Silver plated	0558 992 6	100
4-6 mm ²	6.3 x 0.8 mm	1 PCS	1.6 mm	Tin plated	0558 996 2	100
4-6 mm ²	9.5 x 1.2 mm		1.6 mm	Plain	0558 526 6	50
4-6 mm ²	9.5 x 1.2 mm	1 PCS		Tin plated	0558 526 7	50

Can be stored in ORSY system