

Adhesive lubricant HHS® 2000

Partly synthetic oil that is extremely resistant to high pressures

- Eliminates squeaks and creaks and has excellent flow and penetration performance, as well as good corrosion protection.
- Highly adhesive lubricant that is not spun away when used on turning and rotating parts
- Compatible with O-rings/X-rings and plastics. Neutral behaviour on painted substrates.
- Resistant to splash water and salt water, weak acids and bases
- Free from silicone, resin and acids



Chemical basis	Hydrocarbon
Colour	Yellowish
Smell/fragrance	Oil
Density	0.742 g/cm ³
Density conditions	at 20 °C
Min. temperature conditions	-25 °C
Max. temperature conditions	180 °C
Max. temperature resistance	200 °C
Min. flashing point of active ingredient	300 °C
Kinematic oil basis viscosity	1500 cSt
Silicone-free	Yes
Acid-free	Yes
Resin-free	Yes
AOX-free	Yes
Resistance against	Salt water, Weak lyes, Weak acids, Splash
Container	Can
Shelf life from production	24 Month


Oil basis	Contents	Art. no.	P. Qty.
Mineral oil	500 ml	0893 106	1/6/12 /24
Synthetic mineral oil	150 ml	0893 106 1	1/12

Details/Application

Extremely high-pressure-resistant partly synthetic oil for universal lubrication and for high pressure loads.


Suitable for universal lubrication and for high pressure loads, e.g. shifting, accelerator and clutch linkages, Bowden cables, pins, joints, hinges, reversing levers, lock strikers, drag link ends, slide rails, chain wheels, toothed racks, open gearwheels and much more.

Resistance to high pressure loads



The HHS 2000 lubricating film remains active and does not tear off despite the high pressure load and shearing motion of the base body. Reliably separates the counterpart-body from the base body and thus ensures optimum wear protection at higher pressure loads. This is only possible for dirt-free lubricating points, which is why we recommend a thorough and careful pre-clean with HHS Clean prior to application, art.

Viscosity index



Instructions

Carefully and thoroughly pre-clean lubrication points before each application with HHS Clean art. 089310610. Shake the can before use, spray the parts and let it take effect briefly.

After use, spray the spray head upside down until empty.

The usage instructions are recommendations based on the tests we have conducted and our experience; carry out your own tests before each application. Due to the large number of applications and storage and processing conditions, we do not assume any liability for a specific application result. Insofar as our free customer service provides technical information or acts as an advisory service, no responsibility is assumed by this service except where the advice or information given falls within the scope of our specified, contractually agreed service or the advisor was acting deliberately. We guarantee consistent quality of our products. We reserve the right to make technical changes and further develop products.