


## Pan head tapping screw, C shape with H recessed head

### DIN 7981, galvanised steel, blue passivated (A2K), shape C, with tip

- Tapping screws belong to the thread-moulding screw family. When screwed into a pre-prepared core hole, these screws shape their own counter-thread.
- Guideline values for selecting the correct core hole diameter are contained in DIN 7975.
- Shape C = thread with tip
- Shape F = Thread without tip
- Shape R = Thread with rounded tip



Material	Steel
Surface	Zinc plated
RoHS-compliant	Yes
Form	C



Nominal diameter (d <sub>1</sub> )	Length (l <sub>1</sub> )	Head diameter (d <sub>k</sub> )	Head height (k <sub>1</sub> )	Internal drive	Art. no.	P. Qty.
2.2 mm	4.5 mm	4.2 mm	1.8 mm	H1	<b>0115 22 45</b>	5000
2.2 mm	6.5 mm	4.2 mm	1.8 mm	H1	<b>0115 22 65</b>	1000 /5000
2.2 mm	9.5 mm	4.2 mm	1.8 mm	H1	<b>0115 22 95</b>	300/1000 /2000
2.2 mm	13 mm	4.2 mm	1.8 mm	H1	<b>0115 22 13</b>	1000
2.2 mm	16 mm	4.2 mm	1.8 mm	H1	<b>0115 22 16</b>	2000
2.2 mm	22 mm	4.2 mm	1.8 mm	H1	<b>0115 22 22</b>	1000
2.9 mm	4.5 mm	5.6 mm	2.2 mm	H1	<b>0115 29 45</b>	4000
2.9 mm	6.5 mm	5.6 mm	2.2 mm	H1	<b>0115 29 65</b>	1000 /5000
2.9 mm	9.5 mm	5.6 mm	2.2 mm	H1	<b>0115 29 95</b>	1000 /2000
2.9 mm	13 mm	5.6 mm	2.2 mm	H1	<b>0115 29 13</b>	1000
2.9 mm	16 mm	5.6 mm	2.2 mm	H1	<b>0115 29 16</b>	1000 /2000
2.9 mm	19 mm	5.6 mm	2.2 mm	H1	<b>0115 29 19</b>	1000 /2000
2.9 mm	22 mm	5.6 mm	2.2 mm	H1	<b>0115 29 22</b>	1000 /2000
2.9 mm	25 mm	5.6 mm	2.2 mm	H1	<b>0115 29 25</b>	1000 /2000
2.9 mm	32 mm	5.6 mm	2.2 mm	H1	<b>0115 29 32</b>	1000
2.9 mm	38 mm	5.6 mm	2.2 mm	H1	<b>0115 29 38</b>	2000
3.5 mm	6.5 mm	6.9 mm	2.6 mm	H2	<b>0115 35 65</b>	100/1000 /2000
3.5 mm	9.5 mm	6.9 mm	2.6 mm	H2	<b>0115 35 95</b>	100/1000 /2000
3.5 mm	11 mm	6.9 mm	2.6 mm	H2	<b>0115 35 11</b>	1000
3.5 mm	13 mm	6.9 mm	2.6 mm	H2	<b>0115 35 13</b>	100/1000 /2000

Nominal diameter (d <sub>1</sub> )	Length (l <sub>1</sub> )	Head diameter (d <sub>k</sub> )	Head height (k <sub>1</sub> )	Internal drive	Art. no.	P. Qty.
3.5 mm	16 mm	6.9 mm	2.6 mm	H2	<b>0115 35 16</b>	100/1000 /2000
3.5 mm	19 mm	6.9 mm	2.6 mm	H2	<b>0115 35 19</b>	100/1000 /2000
3.5 mm	22 mm	6.9 mm	2.6 mm	H2	<b>0115 35 22</b>	100/1000 /2000
3.5 mm	25 mm	6.9 mm	2.6 mm	H2	<b>0115 35 25</b>	100/1000 /2000
3.5 mm	32 mm	6.9 mm	2.6 mm	H2	<b>0115 35 32</b>	1000
3.5 mm	38 mm	6.9 mm	2.6 mm	H2	<b>0115 35 38</b>	100/1000
3.5 mm	45 mm	6.9 mm	2.6 mm	H2	<b>0115 35 45</b>	100
3.5 mm	50 mm	6.9 mm	2.6 mm	H2	<b>0115 35 50</b>	100/1000
3.9 mm	6.5 mm	7.5 mm	2.8 mm	H2	<b>0115 39 65</b>	100/1000 /4000
3.9 mm	9.5 mm	7.5 mm	2.8 mm	H2	<b>0115 39 95</b>	100/1000 /2000
3.9 mm	13 mm	7.5 mm	2.8 mm	H2	<b>0115 39 13</b>	100/1000 /2000
3.9 mm	16 mm	7.5 mm	2.8 mm	H2	<b>0115 39 16</b>	100/1000 /2000
3.9 mm	19 mm	7.5 mm	2.8 mm	H2	<b>0115 39 19</b>	100/1000 /2000
3.9 mm	22 mm	7.5 mm	2.8 mm	H2	<b>0115 39 22</b>	100/1000 /2500
3.9 mm	25 mm	7.5 mm	2.8 mm	H2	<b>0115 39 25</b>	100/1000 /2000
3.9 mm	32 mm	7.5 mm	2.8 mm	H2	<b>0115 39 32</b>	100/1000
3.9 mm	38 mm	7.5 mm	2.8 mm	H2	<b>0115 39 38</b>	100/1000
3.9 mm	45 mm	7.5 mm	2.8 mm	H2	<b>0115 39 45</b>	100/500
3.9 mm	50 mm	7.5 mm	2.8 mm	H2	<b>0115 39 50</b>	100/1000
3.9 mm	60 mm	7.5 mm	2.8 mm	H2	<b>0115 39 60</b>	100
3.9 mm	70 mm	7.5 mm	2.8 mm	H2	<b>0115 39 70</b>	100
4.2 mm	6.5 mm	8.2 mm	3.05 mm	H2	<b>0115 42 65</b>	1000 /2000
4.2 mm	9.5 mm	8.2 mm	3.05 mm	H2	<b>0115 42 95</b>	50/100 /1000 /2000
4.2 mm	13 mm	8.2 mm	3.05 mm	H2	<b>0115 42 13</b>	100/1000 /2000
4.2 mm	16 mm	8.2 mm	3.05 mm	H2	<b>0115 42 16</b>	100/1000 /2000
4.2 mm	19 mm	8.2 mm	3.05 mm	H2	<b>0115 42 19</b>	100/1000 /2000
4.2 mm	22 mm	8.2 mm	3.05 mm	H2	<b>0115 42 22</b>	100/1000
4.2 mm	25 mm	8.2 mm	3.05 mm	H2	<b>0115 42 25</b>	100/1000 /2000
4.2 mm	32 mm	8.2 mm	3.05 mm	H2	<b>0115 42 32</b>	100/1000
4.2 mm	35 mm	8.2 mm	3.05 mm	H2	<b>0115 42 35</b>	1000
4.2 mm	38 mm	8.2 mm	3.05 mm	H2	<b>0115 42 38</b>	100/1000
4.2 mm	45 mm	8.2 mm	3.05 mm	H2	<b>0115 42 45</b>	100/1000
4.2 mm	50 mm	8.2 mm	3.05 mm	H2	<b>0115 42 50</b>	50/1000
4.2 mm	60 mm	8.2 mm	3.05 mm	H2	<b>0115 42 60</b>	100
4.2 mm	70 mm	8.2 mm	3.05 mm	H2	<b>0115 42 70</b>	100/500
4.2 mm	80 mm	8.2 mm	3.05 mm	H2	<b>0115 42 80</b>	500
4.8 mm	9.5 mm	9.5 mm	3.55 mm	H2	<b>0115 48 95</b>	100/1000 /2000

Nominal diameter (d <sub>1</sub> )	Length (l <sub>1</sub> )	Head diameter (d <sub>k</sub> )	Head height (k <sub>1</sub> )	Internal drive	Art. no.	P. Qty.
4.8 mm	13 mm	9.5 mm	3.55 mm	H2	<b>0115 48 13</b>	100/1000 /3000
4.8 mm	16 mm	9.5 mm	3.55 mm	H2	<b>0115 48 16</b>	100/1000 /2000
4.8 mm	19 mm	9.5 mm	3.55 mm	H2	<b>0115 48 19</b>	100/1000 /2000
4.8 mm	22 mm	9.5 mm	3.55 mm	H2	<b>0115 48 22</b>	100/400 /1000
4.8 mm	25 mm	9.5 mm	3.55 mm	H2	<b>0115 48 25</b>	100/1000
4.8 mm	32 mm	9.5 mm	3.55 mm	H2	<b>0115 48 32</b>	100/1000
4.8 mm	38 mm	9.5 mm	3.55 mm	H2	<b>0115 48 38</b>	100/500 /1000
4.8 mm	45 mm	9.5 mm	3.55 mm	H2	<b>0115 48 45</b>	100/500
4.8 mm	50 mm	9.5 mm	3.55 mm	H2	<b>0115 48 50</b>	100/500
4.8 mm	60 mm	9.5 mm	3.55 mm	H2	<b>0115 48 60</b>	100
4.8 mm	70 mm	9.5 mm	3.55 mm	H2	<b>0115 48 70</b>	100/250
4.8 mm	80 mm	9.5 mm	3.55 mm	H2	<b>0115 48 80</b>	100/300
4.8 mm	90 mm	9.5 mm	3.55 mm	H2	<b>0115 48 90</b>	100/250
4.8 mm	100 mm	9.5 mm	3.55 mm	H2	<b>0115 48 100</b>	100/200
4.8 mm	110 mm	9.5 mm	3.55 mm	H2	<b>0115 48 110</b>	100
4.8 mm	120 mm	9.5 mm	3.55 mm	H2	<b>0115 48 120</b>	100
5.5 mm	13 mm	10.8 mm	3.95 mm	H3	<b>0115 55 13</b>	500/2000
5.5 mm	16 mm	10.8 mm	3.95 mm	H3	<b>0115 55 16</b>	100/500 /1000
5.5 mm	19 mm	10.8 mm	3.95 mm	H3	<b>0115 55 19</b>	100/500
5.5 mm	22 mm	10.8 mm	3.95 mm	H3	<b>0115 55 22</b>	50/100 /500
5.5 mm	25 mm	10.8 mm	3.95 mm	H3	<b>0115 55 25</b>	100/500 /1000
5.5 mm	32 mm	10.8 mm	3.95 mm	H3	<b>0115 55 32</b>	100/500
5.5 mm	38 mm	10.8 mm	3.95 mm	H3	<b>0115 55 38</b>	100/500
5.5 mm	45 mm	10.8 mm	3.95 mm	H3	<b>0115 55 45</b>	500
5.5 mm	50 mm	10.8 mm	3.95 mm	H3	<b>0115 55 50</b>	500
5.5 mm	60 mm	10.8 mm	3.95 mm	H3	<b>0115 55 60</b>	100
5.5 mm	70 mm	10.8 mm	3.95 mm	H3	<b>0115 55 70</b>	100
5.5 mm	80 mm	10.8 mm	3.95 mm	H3	<b>0115 55 80</b>	100
5.5 mm	90 mm	10.8 mm	3.95 mm	H3	<b>0115 55 90</b>	100
5.5 mm	100 mm	10.8 mm	3.95 mm	H3	<b>0115 55 100</b>	100
5.5 mm	110 mm	10.8 mm	3.95 mm	H3	<b>0115 55 110</b>	100
5.5 mm	120 mm	10.8 mm	3.95 mm	H3	<b>0115 55 120</b>	100
6.3 mm	13 mm	12.5 mm	4.55 mm	H3	<b>0115 63 13</b>	100/1000
6.3 mm	16 mm	12.5 mm	4.55 mm	H3	<b>0115 63 16</b>	100/500
6.3 mm	19 mm	12.5 mm	4.55 mm	H3	<b>0115 63 19</b>	100/500
6.3 mm	22 mm	12.5 mm	4.55 mm	H3	<b>0115 63 22</b>	100/500 /1000
6.3 mm	25 mm	12.5 mm	4.55 mm	H3	<b>0115 63 25</b>	100/500
6.3 mm	32 mm	12.5 mm	4.55 mm	H3	<b>0115 63 32</b>	100/500
6.3 mm	38 mm	12.5 mm	4.55 mm	H3	<b>0115 63 38</b>	500
6.3 mm	45 mm	12.5 mm	4.55 mm	H3	<b>0115 63 45</b>	500
6.3 mm	50 mm	12.5 mm	4.55 mm	H3	<b>0115 63 50</b>	500
6.3 mm	60 mm	12.5 mm	4.55 mm	H3	<b>0115 63 60</b>	100
6.3 mm	70 mm	12.5 mm	4.55 mm	H3	<b>0115 63 70</b>	100
6.3 mm	80 mm	12.5 mm	4.55 mm	H3	<b>0115 63 80</b>	100
6.3 mm	90 mm	12.5 mm	4.55 mm	H3	<b>0115 63 90</b>	100
6.3 mm	100 mm	12.5 mm	4.55 mm	H3	<b>0115 63 100</b>	100

Nominal diameter (d <sub>1</sub> )	Length (l <sub>1</sub> )	Head diameter (d <sub>k</sub> )	Head height (k <sub>1</sub> )	Internal drive	Art. no.	P. Qty.
6.3 mm	110 mm	12.5 mm	4.55 mm	H3	<b>0115 63 110</b>	100
6.3 mm	120 mm	12.5 mm	4.55 mm	H3	<b>0115 63 120</b>	100

Compatible with ORSY storage system