


Hexagon Socket Head Cap Screw

ISO 4762/DIN 912, steel 8.8, galvanised, blue passivated (A2K)

Material	Steel
Surface	Zinc plated
Property class	8.8
RoHS-compliant	Yes



Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M2	5 mm	3.8 mm	2 mm	HS1.5	ISO 4762	0084 2 5	1000
M2	8 mm	3.8 mm	2 mm	HS1.5	ISO 4762	0084 2 8	500
M2	10 mm	3.8 mm	2 mm	HS1.5	ISO 4762	0084 2 10	1000
M2	30 mm	3.8 mm	2 mm	HS1.5	ISO 4762	0084 2 30	500
M2.5	3 mm	4.5 mm	2.5 mm	HS2	ISO 4762	0084 25 3	500
M2.5	4 mm	4.5 mm	2.5 mm	HS2	ISO 4762	0084 25 4	1000
M2.5	5 mm	4.5 mm	2.5 mm	HS2	ISO 4762	0084 25 5	1000
M2.5	6 mm	4.5 mm	2.5 mm	HS2	ISO 4762	0084 25 6	1000
M2.5	8 mm	4.5 mm	2.5 mm	HS2	ISO 4762	0084 25 8	1000
M2.5	10 mm	4.5 mm	2.5 mm	HS2	ISO 4762	0084 25 10	1000
M2.5	16 mm	4.5 mm	2.5 mm	HS2	ISO 4762	0084 25 16	1000
M3	4 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 4	500/1000
M3	5 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 5	500/1000
M3	6 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 6	500/1000
M3	8 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 8	500/1000
M3	10 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 10	500/1000
M3	12 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 12	500/1000
M3	14 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 14	500/1000
M3	16 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 16	500/1000
M3	18 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 18	500/1000
M3	20 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 20	100/500 /1000
M3	22 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 22	100/1000
M3	25 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 25	100/500 /1000
M3	30 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 30	100/500 /1000
M3	35 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 35	200/500
M3	40 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 40	200
M3	45 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 45	200/500
M3	50 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 50	200/500
M3	55 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 55	500
M3	60 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 60	500
M3	65 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 65	200
M3	70 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 70	200

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M3	80 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 80	100
M3	100 mm	5.5 mm	3 mm	HS2.5	ISO 4762	0084 3 100	50
M4	5 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 5	500/1000
M4	6 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 6	100/500/1000
M4	8 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 8	100/500/1000
M4	10 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 10	100/500/2000
M4	12 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 12	100/500/1000
M4	14 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 14	100/500
M4	15 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 15	500
M4	16 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 16	100/500/1000
M4	18 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 18	100/1000
M4	20 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 20	100/500
M4	22 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 22	200/1000
M4	25 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 25	100/500
M4	28 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 28	1000
M4	30 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 30	100/500
M4	35 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 35	100/500/1000
M4	40 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 40	100/500/1000
M4	45 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 45	200
M4	50 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 50	200/500
M4	55 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 55	200
M4	60 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 60	200
M4	65 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 65	200
M4	70 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 70	200
M4	75 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 75	200
M4	80 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 80	200
M4	85 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 85	200
M4	90 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 90	200
M4	95 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 95	200
M4	100 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 100	200
M4	110 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 110	200
M4	120 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 120	200
M4	135 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 135	50
M4	145 mm	7 mm	4 mm	HS3	ISO 4762	0084 4 145	50
M5	6 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 6	100/500
M5	8 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 8	100/500
M5	10 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 10	100/500
M5	12 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 12	100/500
M5	14 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 14	100/500
M5	16 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 16	100/500
M5	18 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 18	100/500
M5	20 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 20	100/500
M5	22 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 22	100/1000
M5	25 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 25	100/500
M5	30 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 30	100/500
M5	35 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 35	100/500
M5	40 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 40	200

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M5	45 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 45	200
M5	50 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 50	200
M5	55 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 55	200
M5	60 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 60	200
M5	64 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 64	500
M5	65 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 65	100/200
M5	70 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 70	100/200
M5	75 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 75	200
M5	80 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 80	100/200
M5	85 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 85	200
M5	90 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 90	100/200
M5	95 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 95	200
M5	100 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 100	100/200
M5	105 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 105	100
M5	110 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 110	100/200
M5	115 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 115	100
M5	120 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 120	100
M5	125 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 125	200
M5	130 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 130	100
M5	135 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 135	100
M5	140 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 140	200
M5	150 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 150	200
M5	160 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 160	200
M5	170 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 170	200
M5	180 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 180	200
M5	190 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 190	25
M5	200 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 200	200
M5	220 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 220	50
M5	240 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 240	50
M5	260 mm	8.5 mm	5 mm	HS4	ISO 4762	0084 5 260	50
M6	5 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 5	500
M6	6 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 6	1000
M6	8 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 8	100/500
M6	10 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 10	100/500
M6	12 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 12	100/500 /1000
M6	14 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 14	100/1000
M6	16 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 16	100/500 /1000
M6	18 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 18	100/500 /1000
M6	20 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 20	100/500 /1000
M6	22 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 22	100/500
M6	25 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 25	100/500
M6	28 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 28	500
M6	30 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 30	100/500
M6	35 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 35	100/200
M6	40 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 40	100/200
M6	45 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 45	200
M6	50 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 50	200
M6	55 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 55	200
M6	60 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 60	200

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M6	65 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 65	200
M6	70 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 70	200
M6	75 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 75	200
M6	80 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 80	100/200
M6	85 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 85	50/100
M6	90 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 90	50/200
M6	95 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 95	100
M6	100 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 100	50/100
M6	105 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 105	100
M6	110 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 110	100
M6	115 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 115	100
M6	120 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 120	100
M6	125 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 125	100
M6	130 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 130	100
M6	135 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 135	100
M6	140 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 140	100
M6	145 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 145	100
M6	150 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 150	100
M6	160 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 160	100
M6	165 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 165	100
M6	170 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 170	100
M6	175 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 175	10
M6	180 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 180	100
M6	185 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 185	100
M6	190 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 190	100
M6	195 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 195	100
M6	200 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 200	100
M6	205 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 205	100
M6	210 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 210	100
M6	220 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 220	50
M6	240 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 240	100
M6	245 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 245	100
M6	250 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 250	50
M6	260 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 260	100
M6	270 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 270	100
M6	280 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 280	100
M6	300 mm	10 mm	6 mm	HS5	ISO 4762	0084 6 300	100
M8	8 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 8	200
M8	10 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 10	50/500
M8	12 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 12	200
M8	14 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 14	100/200
M8	16 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 16	200/500
M8	18 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 18	200
M8	20 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 20	200
M8	22 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 22	100/500
M8	25 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 25	200
M8	30 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 30	100/400
M8	35 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 35	200
M8	40 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 40	200
M8	45 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 45	200
M8	50 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 50	200
M8	55 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 55	100/200
M8	60 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 60	100/200

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M8	65 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 65	100/200
M8	70 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 70	100/200
M8	75 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 75	100
M8	80 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 80	100/200
M8	85 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 85	100
M8	90 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 90	100
M8	95 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 95	100
M8	100 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 100	100
M8	105 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 105	100
M8	110 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 110	100
M8	115 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 115	100
M8	120 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 120	100
M8	125 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 125	100
M8	130 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 130	50/100
M8	135 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 135	50
M8	140 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 140	100
M8	145 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 145	100
M8	150 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 150	50/100
M8	155 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 155	100
M8	160 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 160	50
M8	165 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 165	50
M8	170 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 170	50
M8	175 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 175	100
M8	180 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 180	50
M8	185 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 185	50
M8	200 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 200	50
M8	210 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 210	50
M8	220 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 220	50
M8	230 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 230	100
M8	240 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 240	50
M8	250 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 250	100
M8	260 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 260	25
M8	270 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 270	100
M8	280 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 280	100
M8	300 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 300	50
M8	310 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 310	50
M8	320 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 320	10
M8	370 mm	13 mm	8 mm	HS6	ISO 4762	0084 8 370	100
M10	10 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 10	200
M10	12 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 12	200
M10	14 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 14	200
M10	16 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 16	200
M10	18 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 18	200
M10	20 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 20	200
M10	22 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 22	200
M10	25 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 25	200
M10	30 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 30	200
M10	35 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 35	50/200
M10	40 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 40	50/100 /200
M10	45 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 45	100
M10	50 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 50	100
M10	55 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 55	100

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M10	60 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 60	100
M10	65 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 65	100
M10	70 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 70	100
M10	75 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 75	50/100
M10	80 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 80	100
M10	85 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 85	50/100
M10	90 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 90	100
M10	95 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 95	50
M10	100 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 100	50/100
M10	105 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 105	50
M10	110 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 110	50
M10	115 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 115	50
M10	120 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 120	50
M10	125 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 125	50
M10	130 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 130	50
M10	135 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 135	100
M10	140 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 140	25/50
M10	150 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 150	25
M10	155 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 155	100
M10	160 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 160	25
M10	165 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 165	100
M10	170 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 170	100
M10	180 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 180	25/50
M10	185 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 185	10
M10	190 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 190	50
M10	195 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 195	25
M10	200 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 200	50
M10	210 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 210	25
M10	220 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 220	50
M10	240 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 240	25
M10	250 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 250	25
M10	260 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 260	25
M10	270 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 270	25
M10	280 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 280	25
M10	300 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 300	25
M10	320 mm	16 mm	10 mm	HS8	ISO 4762	0084 10 320	10
M12	10 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 10	100
M12	16 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 16	50/200
M12	20 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 20	50/100
M12	22 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 22	100
M12	25 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 25	50/200
M12	30 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 30	50/100 /200
M12	35 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 35	50/100 /200
M12	40 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 40	100
M12	45 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 45	100
M12	50 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 50	100
M12	55 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 55	100
M12	60 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 60	100
M12	65 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 65	50/100
M12	70 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 70	50
M12	75 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 75	50

Cl01_3511140108_Rev. 0.298_Statel: 06. 10. 2022

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M12	80 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 80	50
M12	85 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 85	50
M12	90 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 90	50
M12	95 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 95	50
M12	100 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 100	50
M12	105 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 105	50
M12	110 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 110	25/50
M12	115 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 115	50
M12	120 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 120	50
M12	125 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 125	100
M12	130 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 130	50
M12	135 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 135	50
M12	140 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 140	50
M12	145 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 145	25
M12	150 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 150	25/50
M12	155 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 155	100
M12	160 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 160	25
M12	170 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 170	25
M12	180 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 180	25
M12	200 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 200	25
M12	220 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 220	25
M12	230 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 230	25
M12	240 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 240	25
M12	250 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 250	50
M12	260 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 260	25
M12	280 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 280	25
M12	290 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 290	25
M12	300 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 300	25
M12	320 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 320	25
M12	360 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 360	25
M12	400 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 400	25
M12	550 mm	18 mm	12 mm	HS10	ISO 4762	0084 12 550	10
M14	20 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 20	100
M14	25 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 25	100
M14	30 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 30	100
M14	35 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 35	100
M14	40 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 40	100
M14	45 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 45	50
M14	50 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 50	50
M14	55 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 55	50
M14	60 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 60	50
M14	65 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 65	25
M14	70 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 70	50
M14	80 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 80	50
M14	85 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 85	50
M14	90 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 90	25
M14	100 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 100	50
M14	110 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 110	25
M14	120 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 120	25
M14	130 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 130	25
M14	140 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 140	50
M14	145 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 145	25
M14	150 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 150	25

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M14	160 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 160	25
M14	200 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 200	25
M14	260 mm	21 mm	14 mm	HS12	ISO 4762	0084 14 260	25
M16	20 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 20	50
M16	25 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 25	50
M16	30 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 30	50
M16	35 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 35	50
M16	40 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 40	50
M16	45 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 45	50
M16	50 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 50	50
M16	55 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 55	50
M16	60 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 60	50
M16	65 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 65	25/50
M16	70 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 70	25/50
M16	75 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 75	50
M16	80 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 80	25/50
M16	85 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 85	50
M16	90 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 90	25/50
M16	95 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 95	25
M16	100 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 100	25
M16	105 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 105	10
M16	110 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 110	25
M16	120 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 120	25
M16	125 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 125	25
M16	130 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 130	25
M16	140 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 140	25
M16	150 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 150	25
M16	160 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 160	25
M16	165 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 165	10
M16	170 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 170	25
M16	180 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 180	25
M16	185 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 185	1
M16	190 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 190	25
M16	200 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 200	15
M16	210 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 210	25
M16	220 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 220	25
M16	230 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 230	25
M16	240 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 240	25
M16	250 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 250	25
M16	260 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 260	25
M16	280 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 280	25
M16	290 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 290	25
M16	310 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 310	25
M16	340 mm	24 mm	16 mm	HS14	ISO 4762	0084 16 340	10
M18	30 mm	27 mm	18 mm	HS14	DIN 912	0084 18 30	25
M18	35 mm	27 mm	18 mm	HS14	DIN 912	0084 18 35	50
M18	40 mm	27 mm	18 mm	HS14	DIN 912	0084 18 40	50
M18	50 mm	27 mm	18 mm	HS14	DIN 912	0084 18 50	25
M18	60 mm	27 mm	18 mm	HS14	DIN 912	0084 18 60	25
M18	65 mm	27 mm	18 mm	HS14	DIN 912	0084 18 65	25
M18	80 mm	27 mm	18 mm	HS14	DIN 912	0084 18 80	25
M18	130 mm	27 mm	18 mm	HS14	DIN 912	0084 18 130	25
M18	160 mm	27 mm	18 mm	HS14	DIN 912	0084 18 160	15

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M20	30 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 30	25/50
M20	35 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 35	25
M20	40 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 40	25
M20	45 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 45	25
M20	50 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 50	25
M20	55 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 55	25
M20	60 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 60	25
M20	65 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 65	25
M20	70 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 70	25
M20	75 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 75	25
M20	80 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 80	25
M20	85 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 85	25
M20	90 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 90	25
M20	100 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 100	25
M20	110 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 110	25
M20	120 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 120	25
M20	130 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 130	25
M20	140 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 140	25
M20	150 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 150	25
M20	160 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 160	10
M20	170 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 170	10
M20	180 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 180	10
M20	190 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 190	10
M20	200 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 200	10
M20	210 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 210	10
M20	220 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 220	10
M20	240 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 240	10
M20	250 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 250	10
M20	260 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 260	10
M20	270 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 270	10
M20	290 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 290	10
M20	300 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 300	10
M20	320 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 320	5
M20	360 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 360	10
M20	400 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 400	25
M20	480 mm	30 mm	20 mm	HS17	ISO 4762	0084 20 480	10
M22	140 mm	33 mm	22 mm	HS17	DIN 912	0084 22 140	10
M24	40 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 40	25
M24	45 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 45	25
M24	50 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 50	25
M24	55 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 55	25
M24	60 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 60	25
M24	65 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 65	25
M24	70 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 70	25
M24	75 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 75	25
M24	80 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 80	10/25
M24	85 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 85	25
M24	90 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 90	1/10/25
M24	95 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 95	10
M24	100 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 100	1/10
M24	110 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 110	10
M24	120 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 120	10
M24	130 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 130	10

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M24	140 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 140	10
M24	150 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 150	10
M24	160 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 160	10
M24	170 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 170	10
M24	180 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 180	10
M24	190 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 190	10
M24	200 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 200	10
M24	220 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 220	10
M24	240 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 240	10
M24	250 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 250	10
M24	260 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 260	10
M24	270 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 270	10
M24	280 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 280	10
M24	300 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 300	10
M24	320 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 320	10
M24	350 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 350	10
M24	360 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 360	10
M24	400 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 400	10
M24	420 mm	36 mm	24 mm	HS19	ISO 4762	0084 24 420	1
M27	45 mm	66 mm	27 mm	HS19	DIN 912	0084 27 45	10
M27	50 mm	66 mm	27 mm	HS19	DIN 912	0084 27 50	10
M27	55 mm	66 mm	27 mm	HS19	DIN 912	0084 27 55	10
M27	60 mm	66 mm	27 mm	HS19	DIN 912	0084 27 60	10
M27	70 mm	66 mm	27 mm	HS19	DIN 912	0084 27 70	10
M27	80 mm	66 mm	27 mm	HS19	DIN 912	0084 27 80	10
M27	90 mm	66 mm	27 mm	HS19	DIN 912	0084 27 90	10
M27	100 mm	66 mm	27 mm	HS19	DIN 912	0084 27 100	10
M27	110 mm	66 mm	27 mm	HS19	DIN 912	0084 27 110	10
M27	120 mm	66 mm	27 mm	HS19	DIN 912	0084 27 120	10
M27	130 mm	66 mm	27 mm	HS19	DIN 912	0084 27 130	10
M27	140 mm	66 mm	27 mm	HS19	DIN 912	0084 27 140	10
M27	150 mm	66 mm	27 mm	HS19	DIN 912	0084 27 150	10
M27	160 mm	66 mm	27 mm	HS19	DIN 912	0084 27 160	10
M27	180 mm	66 mm	27 mm	HS19	DIN 912	0084 27 180	10
M27	200 mm	66 mm	27 mm	HS19	DIN 912	0084 27 200	10
M30	45 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 45	10
M30	50 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 50	10
M30	55 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 55	10
M30	60 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 60	10
M30	65 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 65	10
M30	70 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 70	10
M30	75 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 75	10
M30	80 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 80	10
M30	90 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 90	10
M30	95 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 95	10
M30	100 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 100	10
M30	110 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 110	10
M30	120 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 120	10
M30	125 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 125	10
M30	130 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 130	10
M30	140 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 140	10
M30	150 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 150	10
M30	160 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 160	10

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M30	170 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 170	10
M30	180 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 180	10
M30	200 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 200	5
M30	210 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 210	10
M30	220 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 220	10
M30	230 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 230	1
M30	240 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 240	10
M30	260 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 260	10
M30	300 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 300	10
M30	320 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 320	1
M30	340 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 340	5
M30	400 mm	45 mm	30 mm	HS22	ISO 4762	0084 30 400	5
M33	90 mm	50 mm	33 mm	HS24	DIN 912	0084 33 90	10
M33	160 mm	50 mm	33 mm	HS24	DIN 912	0084 33 160	5
M36	55 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 55	10
M36	60 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 60	10
M36	65 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 65	1
M36	70 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 70	10
M36	80 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 80	10
M36	90 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 90	10
M36	100 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 100	10
M36	110 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 110	10
M36	120 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 120	10
M36	130 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 130	10
M36	140 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 140	10
M36	150 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 150	10
M36	160 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 160	5
M36	170 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 170	10
M36	180 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 180	10
M36	200 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 200	10
M36	220 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 220	5
M36	240 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 240	10
M36	260 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 260	10
M36	280 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 280	10
M36	300 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 300	10
M36	350 mm	54 mm	36 mm	HS27	ISO 4762	0084 36 350	1
M42	70 mm	63 mm	42 mm	HS32	ISO 4762	0084 42 70	10
M42	80 mm	63 mm	42 mm	HS32	ISO 4762	0084 42 80	1
M42	90 mm	63 mm	42 mm	HS32	ISO 4762	0084 42 90	5
M42	100 mm	63 mm	42 mm	HS32	ISO 4762	0084 42 100	1
M42	110 mm	63 mm	42 mm	HS32	ISO 4762	0084 42 110	1
M42	120 mm	63 mm	42 mm	HS32	ISO 4762	0084 42 120	5
M42	150 mm	63 mm	42 mm	HS32	ISO 4762	0084 42 150	1
M42	200 mm	63 mm	42 mm	HS32	ISO 4762	0084 42 200	5
M42	220 mm	63 mm	42 mm	HS32	ISO 4762	0084 42 220	1
M42	260 mm	63 mm	42 mm	HS32	ISO 4762	0084 42 260	5
M42	500 mm	63 mm	42 mm	HS32	ISO 4762	0084 42 500	5
M48	100 mm	72 mm	48 mm	HS36	ISO 4762	0084 48 100	5
M48	110 mm	72 mm	48 mm	HS36	ISO 4762	0084 48 110	5
M48	140 mm	72 mm	48 mm	HS36	ISO 4762	0084 48 140	5
M48	150 mm	72 mm	48 mm	HS36	ISO 4762	0084 48 150	1
M48	240 mm	72 mm	48 mm	HS36	ISO 4762	0084 48 240	1
M48	250 mm	72 mm	48 mm	HS36	ISO 4762	0084 48 250	1

Thread type x nominal diameter (d ₁)	Length (l ₁)	Head diameter (d _k)	Head height (k ₁)	Internal drive (s ₁)	Standards	Art. no.	P. Qty.
M48	350 mm	72 mm	48 mm	HS36	ISO 4762	0084 48 350	1
M48	580 mm	72 mm	48 mm	HS36	ISO 4762	0084 48 580	1
M56	80 mm	84 mm	56 mm	HS41	ISO 4762	0084 56 80	5
M56	100 mm	84 mm	56 mm	HS41	ISO 4762	0084 56 100	1
M56	120 mm	84 mm	56 mm	HS41	ISO 4762	0084 56 120	1
M56	140 mm	84 mm	56 mm	HS41	ISO 4762	0084 56 140	1
M56	160 mm	84 mm	56 mm	HS41	ISO 4762	0084 56 160	1
M56	200 mm	84 mm	56 mm	HS41	ISO 4762	0084 56 200	1
M64	140 mm	96 mm	64 mm	HS46	ISO 4762	0084 64 140	1
M64	180 mm	96 mm	64 mm	HS46	ISO 4762	0084 64 180	1

Notice

ISO 4762 replaces DIN 912 | There is some similarity | Nominal range changed | Fine thread moved to ISO 12474.