


Serrated locking nut

Plain A2 stainless steel with locking teeth

Material	Stainless steel A2
Property class	50
Surface	Plain
RoHS-compliant	Yes
Locking device operating principle	Serration
Locking function	Locking against self-loosening by mechanical interlocking



Thread type x nominal diameter (D)	Height (h ₁)	Flange diameter (d _c)	External drive (s ₁)	Standards	Pitch	Art. no.	P. Qty.
M3	4 mm	8 mm	WS5.5	DIN Similar to 6923	0.5 mm	0387 000 03	2000
M4	4 mm	10.41 mm	WS7	DIN Similar to 6923	0.7 mm	0387 000 04	1000
M5	5 mm	11.8 mm	WS8	DIN Similar to 6923	0.8 mm	0387 000 05	250/1000
M6	6 mm	14.2 mm	WS10	DIN Similar to 6923	1 mm	0387 000 06	200/250 /1000
M8	8 mm	17.9 mm	WS13	DIN Similar to 6924	1.25 mm	0387 000 08	250/500
M10	10 mm	21.8 mm	WS15	DIN Similar to 6923	1.5 mm	0387 000 010	100/500
M12	12 mm	26 mm	WS18	DIN Similar to 6923	1.75 mm	0387 000 012	100/200

Details/Application



Notice

DIN 6923 has been withdrawn and replaced by EN 1661. There is some similarity (Fine thread removed | Width across flats for size M10 changed from 15 mm to 16 mm).